



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 50MR16TFL35C(EXN 50W 12V Hal MR16 GU5.3 Bi-Pin Base Reflector Cover *Sylvania-Ledvance*

Catalog Number	50MR16TFL35C(EXN
Manufacturer	Sylvania-Ledvance
Description	Tungsten Halogen Tru Aim MR16 Titan Axial Filament Uv Filter Hard Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 50WATT 12VOLT Flood Beam
Weight per unit	0.0900 (lbs/each)
Product Category	Halogen Reflector Ar, BR, JDR,

### Features

average life	4000
Base	GU5.3 Bipin
beam angle	36
dimnable	Yes
Lamp Type	MR16
lumens	900
Shape	MR16
start type	Instant
Voltage	12.00 V
Voltage Rating	12
Wattage	50

### Material, Color, and Finish

color rendering index (cri)	100
color temperature	3000

### Descriptions

Description	50W 12V HAL MR16 GU5.3 BI-PIN BASE REFLECTOR COVER
extra long description	SYL 50MR16TFL35CEXN-12V/58309 50MR1
Long Description	Tungsten Halogen Tru Aim MR16 TITAN Axial Filament UV Filter Hard Dichroic Reflector Cover Glass GU5.3 Bi Pin Base 50Watt 12Volt Flood Beam
Product Type	50MR16TFL35CEXN 12V 20/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135583094
Manufacturers Part Number	50MR16/T/FL35/C(EXN)-12V/58309
UPC	046135583094



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... QUARTZ

Type ..... HALOGEN

## Packaging

Carton ..... 1

Package ..... 20

Weight Per each ..... 0.09

## Uses, Certifications, and Standards

Application ..... Medium Screwbase or bi-pin

standard ..... EXN