



**Product Number:** 16125

**Order Abbreviation:** 50PAR30/HAL/S/NFL25 120V

**General Description:** Tungsten Halogen PAR30 Silver Reflector Lamp 50Watt 120Volt Medium Base NarrowFlood25 Beam

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	50PAR30HALSNFL25 120V 10/CS 1/SKU
Approx. Lumens	850
Average Rated Life (hr)	1500
Base	E26 Medium
Beam Angle (deg)	25
Beam Type	NFL
Bulb	PAR30
Centerbeam Candlepower (cp)	2600
Class	C (gas)
Color Rendering Index (CRI)	99
Color Temperature/CCT (K)	2875
Diameter (in)	3.752
Diameter (mm)	95.30
Ecologic	YES
Family Brand Name	Halogen Par30
Filament	CC-8
Horizontal Beam Angle (deg)	25
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	3.625
Maximum Overall Length - MOL (mm)	92.075
Nominal Voltage (V)	120.00
Nominal Wattage (W)	50.00
Vertical Beam Angle (deg)	25



#### Footnotes

- State of the Art SPL Optics
- In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.



**Product Number:** 16125

**Order Abbreviation:** 50PAR30/HAL/S/NFL25 120V

**General Description:** Tungsten Halogen PAR30 Silver Reflector Lamp 50Watt 120Volt Medium Base NarrowFlood25 Beam

**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	50PAR30HALSNFL25 120V 10/CS 1/SKU
Approx. Lumens	850
Average Rated Life (hr)	1500
Base	E26 Medium
Beam Angle (deg)	25
Beam Type	NFL
Bulb	PAR30
Centerbeam Candlepower (cp)	2600
Class	C (gas)
Color Rendering Index (CRI)	99
Color Temperature/CCT (K)	2875
Diameter (in)	3.752
Diameter (mm)	95.30
Ecologic	YES
Family Brand Name	Halogen Par30
Filament	CC-8
Horizontal Beam Angle (deg)	25
Lamp Finish	Reflector
Maximum Overall Length - MOL (in)	3.625
Maximum Overall Length - MOL (mm)	92.075
Nominal Voltage (V)	120.00
Nominal Wattage (W)	50.00
Vertical Beam Angle (deg)	25



#### Footnotes

- State of the Art SPL Optics
- In base up operation, heat may eventually deteriorate paper-lined or plastic sockets.