



T-GRID BOX HANGER, 24" T-GRID SPAN

CATALOG NUMBER

512



FEATURES

Dual height feature permits 1-1/2" (38 mm) deep electrical box to be mounted flush with tile or offset 3/4" (19 mm) for plaster ring

Allows 2-1/8" (54 mm) deep electrical box to be mounted flush with tile

Snaps easily onto T-Grid

Hanger comes complete with box mounting clip and screw

PRODUCT ATTRIBUTES

Material: Steel;Spring Steel

Finish: Pregalvanized;nVent CADDY Armour

T-Grid Span: 24"


Ultimate Static Load (F): 20lb

ADDITIONAL PRODUCT DETAILS

Not to exceed static load without independent wire support to box mounting clip.

Not permitted for paddle fans.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF

TRACER