



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 523WG 20A 120/277VAC S Wire Comm 3W SW W

*Pass & Seymour/Legrand*

Catalog Number	523WG
Manufacturer	Pass & Seymour/Legrand
Description	Commercial 3WAY Switch, Side Wire, 20AMP 120/277VOLT, White.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Switches

### Features

action	Three pole
amperage rating	20
connection	Side Wire or external screw-pressure plate
Connection Type	Wired
Contact Configuration	One piece brass alloy contact arm
Contact Rating	Oversized silver alloy contacts
Degree of Protection	1500V Dielectric Withstand Voltage
indoor/outdoor	Indoor
insulation	False
Material	Thermoplastic
media	Yes
Poles	3-way
Switch Type	Toggle
Voltage	120/277 V
Voltage Rating	120/277

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 120/277VAC S WIRE COMM 3W SW W
extra long description	P&S CS20AC3W 20A 120/277VAC S WIRE
Long Description	Commercial 3way Switch, Side Wire, 20amp 120/277volt, White.
Product Type	20A 120/277VAC S Wire Comm 3W SW W
Special Features	Back & Side wire, locking support, one piece brass alloy contact arm

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007126556
Manufacturers Part Number	CS20AC3W
UPC	785007126556



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	SWITCH

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.15

## Uses, Certifications, and Standards

Application	Commercial
Enclosure	Nylon
Mounting	WALL
nema rating	WD-1 and WD-6
standard	CULUS, FEDSPEC, UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2