



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5262I Duplex Recp 15A 125V S+B Wire Iv

Pass & Seymour/Legrand

| | |
|------------------|-------------------------------------------------------------------|
| Catalog Number | 5262I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Hard Use Spec Grade Duplex Receptacle Back and Side Wire 15A 125V |
| Weight per unit | 0.2032 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--------------------------------------------------|
| amperage rating | 15 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| Number of Wires | 3 |
| Outlet Type | Commercial, Indoor |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Ivory |
|-------|-------|

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | .780 |

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | DUPLEX RECP 15A 125V S+B WIRE IV |
| extra long description | P&S 5262I RECP DUP 15A 125V S+B WIR |
| Long Description | Hard Use Spec Grade Duplex Receptacle Back and Side Wire 15A 125V |
| Product Type | Recp Dup 15A 125V S+B Wire Iv |
| Special Features | Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face. 8 hole internal screw-pressure-plate back wire terminals accept #14 – #10 AWG solid or stranded copper or copper-clad conductors. Terminal compartments isolated from each other for posi |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007526219 |
| Manufacturers Part Number | 5262-I |
| UPC | 785007526219 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.2032 |

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-15R |
| standard | FEDSPEC, CULUS, UL498, CSA C22.2 No. 42, FEDSPEC |
| Temperature Rating | -40° - 60° C |