



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5262W Duplex Recp 15A 125V S+B Wire WH

*Pass & Seymour/Legrand*

|                  |   |
|------------------|---|
| Catalog Number   | 5262W   |
| Manufacturer     | Pass & Seymour/Legrand  |
| Description      | Hard Use Spec Grade Duplex Receptacle Back and Side Wire 15A 125V |
| Weight per unit  | 0.2032 (lbs/each)   |
| Product Category | Gen Purpose Recept & Surge Pro                                    |

### Features

|                     |  |
|---------------------|--|
| amperage rating     | 15   |
| connection          | Back and side wire                               |
| Dielectric Strength | Withstands 2000V minimum                         |
| indoor/outdoor      | Indoor   |
| Material            | Nylon  |
| media               | Yes  |
| Number of Wires     | 3  |
| Outlet Type         | Commercial, Indoor                               |
| Poles               | 2  |
| Voltage             | 125.0 V  |
| Voltage Rating      | 125  |
| Wattage             | Electrical power is expressed in Amps and Volts. |
| Wire Size           | 14 - 10  |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | White |
| Finish | Matte |

### Dimensions and Weight

|        |       |
|--------|-------|
| Height | 3.281 |
| Width  | .780  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | DUPLEX RECP 15A 125V S+B WIRE WH  |
| extra long description | P&S 5262W RECEPT DUPLEX 15A 125V S+   |
| Long Description       | Hard Use Spec Grade Duplex Receptacle Back and Side Wire 15A 125V   |
| Product Type           | Recept Duplex 15A 125V S+B Wire WH  |
| Special Features       | Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face. 8 hole internal screw-pressure-plate back wire terminals accept #14 – #10 AWG solid or stranded copper or copper-clad conductors. Terminal compartments isolated from each other for posi |

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007526271   |
| Manufacturers Part Number | 5262-W           |
| UPC                       | 785007526271     |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type                 | Outlet                 |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 10     |
| Package         | 100    |
| Weight Per each | 0.2032 |

## Uses, Certifications, and Standards

|                          |                                |
|--------------------------|--------------------------------|
| Application              | Commercial                     |
| environmental conditions | Flammability: UL94 V2          |
| Mounting                 | WALL                           |
| nema rating              | 5-15R                          |
| standard                 | CULUS, UL498, CSA C22.2 No. 42 |
| Temperature Rating       | -40° - 60° C                   |