

---

## 15A, 125V EXTRA-HARD USE SPEC-GRADE PLUG, WHITE FACE

PS5266X | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Straight Blade Plug 2pole 3wire 15amp 125v



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White, Black

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121402

#### DIMENSIONS

Depth (US): 1.752"

Height (US): 1.516"  
Width (US): 1.516"

#### TECHNICAL INFORMATION

NEMA Configuration Number: 5-15P  
Volts (AC): 125  
Grade Type: Specification

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant



---

## 15A, 125V EXTRA-HARD USE SPEC-GRADE PLUG, WHITE FACE

PS5266X | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Straight Blade Plug 2pole 3wire 15amp 125v



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White, Black

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121402

#### DIMENSIONS

Depth (US): 1.752"

Height (US): 1.516"  
Width (US): 1.516"

#### TECHNICAL INFORMATION

NEMA Configuration Number: 5-15P  
Volts (AC): 125  
Grade Type: Specification

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

