



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5266XHG Straight Blade Plug 3W 15A 125V HG

Pass & Seymour/Legrand

Catalog Number	5266XHG
Manufacturer	Pass & Seymour/Legrand
Description	Straight Blade Hospital Grade Plug, Double Pole Andthree Wire, Unit Arrives Completely Ready-to-Wire, Cutting Installation Time Significantly. Its Nylon Housing Provides Impact and Chemical Resistance. Its Rugged Two-Piece Cord Grip Provides More Uniform Cord Retention Andthe Internal Dust Shield Keeps Terminals Free Of Contaminants. 15AMP 125VOLT.
Weight per unit	0.1600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Wire Grounding
Material	Nylon
Number of Wires	3
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	4

Dimensions and Weight

Size	2.8 in
------	--------

Descriptions

Description	STR BLD PLUG 3W 15A 125V HG
extra long description	P&S PS5266XHG STR BLD PLUG 3W 15A 1
Long Description	Straight Blade Hospital Grade Plug, double pole andthree wire, unit arrives completely ready-to-wire, cutting installation time significantly. Its nylon housing provides impact and chemical resistance. Its rugged two-piece cord grip provides more uniform cord retention andthe internal dust shield keeps terminals free of contaminants. 15amp 125volt.
Product Type	STR BLD Plug 3W 15A 125V HG
Special Features	Ready to wire, rugged 2pc cord grip\

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007236774
Manufacturers Part Number	PS5266XHG
UPC	785007236774



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Hospital Grade Plug Straight Blade

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.16

Uses, Certifications, and Standards

Application	Extra Hard Use
nema rating	5-15P
standard	FEDSPEC, CULUS, UL 498, FEDSPEC