


# Hospital grade plugs and connectors

## Quick grip hospital grade plugs & connectors

### Product description

2-pole, 3-wire grounding  
15A, 125V/AC; 20A, 125V/AC  
NEMA 5-15, 5-20



AH8115W

### Design features

- Single-piece hinged body reduces number of assembly screws to speed installation
- Unique terminal configuration places screws in only two directions, reducing installation time
- Clear terminal cover and large, funneled wire entry ensures quick and accurate wiring
- Signature exterior design molds to hand with scallop feature for extra grip for insertion and removal
- Superior materials and rugged construction provide abuse resistance and reliable performance

### Quick grip plugs & connectors



Rating								
A	V/AC	NEMA	Description	Cord diameter	Color	Catalog no.		
15	125	5-15	Quick grip plug	0.22"-0.67" (5.6-16.9mm)	W	□ AH8115W	•	
			Quick grip connector	0.22"-0.67" (5.6-16.9mm)	W	□ AH8119W	•	



5266NHG

## Auto grip hospital grade plugs & connectors

### Product description

2-pole, 3-wire grounding  
15A, 125V/AC; 20A, 125V/AC  
NEMA 5-15, 5-20

### Design features

- Neoprene gasket seals cord hole opening to ensure strong sealing of wiring chamber
- Automatic cord grip assembly clamps the flexible cord to reduce wiring time, saving time and money
- Combination head screws: U.S. Phillips/Slotted; Canadian Robertson/Slotted
- Tapered body reduces snagging and provides easy handling



5269NHG

### Auto grip plugs & connectors



Rating								
A	V/AC	NEMA	Description	Cord diameter	Color	Catalog no.		
15	125	5-15	Auto grip straight body plug	0.30"-0.66" (7.6-16.7mm)	BK & W	□ 5266NHG	•	
			Auto grip isolated ground plug	0.30"-0.66" (7.6-16.7mm)	RN	□ IG5266NHG	•	
			Auto grip straight body connector	0.30"-0.66" (7.6-16.7mm)	BK & W	□ 5269NHG	•	
20	125	5-20	Auto grip straight body plug	0.30"-0.66" (7.6-16.7mm)	BK & W	□ 5366NHG	•	•
			Auto grip straight body connector	0.30"-0.66" (7.6-16.7mm)	BK & W	□ 5369NHG	•	•

### Color ordering information

BK (Black), RN (Orange), W (White)



**Testing & code compliance:** Listed to UL498, file no. E3663, E146159 (Quick grip series), UL verified to Federal Spec. WC-596F, CSA certified to C22.2, no. 42. (Quick grip series). **Material characteristics:** Nylon, Environmental: Flammability meets UL94 requirements; Quick grip V2 rated, auto grip V2 rated, Temperature rating: quick grip -40°C to 75°C (-40°F to 167°F).



**Compliances, specifications and availability are subject to change without notice.**