



## COMMERCIAL SPEC GRADE RECEPTACLE, SIDE WIRE, 20A, 125V, BROWN

CR20 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Commercial Spec Grade Duplex Receptacle, Side Wire 20amp 125volt, Brown



- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Type: Receptacles  
Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes

UN SPSC: 39121406

UR: No

## DIMENSIONS

Depth (US): 0.78"

Height (US): 3.281"

Width (US): 1.322"

## TECHNICAL INFORMATION

Amps: 20A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## COMMERCIAL SPEC GRADE RECEPTACLE, SIDE WIRE, 20A, 125V, BROWN

CR20 | [Pass & Seymour](#)

### FEATURES & BENEFITS

Commercial Spec Grade Duplex Receptacle, Side Wire 20amp 125volt, Brown



- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Brown  
Type: Receptacles  
Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes

UN SPSC: 39121406

UR: No

## DIMENSIONS

Depth (US): 0.78"

Height (US): 3.281"

Width (US): 1.322"

## TECHNICAL INFORMATION

Amps: 20A

Volts: 125V

Volts (AC): 125

Capacity: Duplex

Grade Type: Commercial

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

