



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5362BK Duplex Recp 20A 125V S+B Wire BK

*Pass & Seymour/LeGrand*

|                  |   |
|------------------|---|
| Catalog Number   | 5362BK  |
| Manufacturer     | Pass & Seymour/LeGrand  |
| Description      | Extra Hard Use Spec Grade 20A 125V Duplex Receptacle Back and Side Wire |
| Weight per unit  | 0.2411 (lbs/each)   |
| Product Category | Gen Purpose Recept & Surge Pro  |

### Features

|                     |  |
|---------------------|--|
| amperage rating     | 20   |
| connection          | Back and side wire                               |
| Dielectric Strength | Withstands 2000V minimum                         |
| indoor/outdoor      | Indoor   |
| Material            | Nylon  |
| Number of Wires     | 3  |
| Outlet Type         | Indoor, Commercial                               |
| Poles               | 2  |
| Voltage             | 125.0 V  |
| Voltage Rating      | 125  |
| Wattage             | Electrical power is expressed in Amps and Volts. |
| Wire Size           | 14 - 10  |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | Black |
| Finish | Matte |

### Dimensions and Weight

|        |       |
|--------|-------|
| Height | 3.281 |
| Width  | .780  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | DUPLEX RECP 20A 125V S+B WIRE BK  |
| extra long description | P&S 5362BK RECEPT DUP 20A 125V S+B  |
| Long Description       | Extra Hard Use Spec Grade 20A 125V Duplex Receptacle Back and Side Wire   |
| Product Type           | Recept Dup 20A 125V S+B Wire BK   |
| Special Features       | Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face. 8 hole internal screw-pressure-plate back wire terminals accept #14 – #10 AWG solid or stranded copper or copper-clad conductors. Terminal compartments isolated from each other for posi |

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Pass and Seymour |
| GTIN                      | 00785007536232   |
| Manufacturers Part Number | 5362-BK          |
| UPC                       | 785007536232     |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type                 | Outlet                 |

## Trade Size

|          |      |
|----------|------|
| Amperage | 20.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 100    |
| Weight Per each | 0.2411 |

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Commercial                                       |
| environmental conditions | Flammability: UL94 V2                            |
| Mounting                 | WALL   |
| nema rating              | 5-20R  |
| standard                 | FEDSPEC, CULUS, UL498, CSA C22.2 No. 42, FEDSPEC |
| Temperature Rating       | -40° - 60° C                                     |