



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5362ISP TVSS Recp 20A 125V Alarm Iv

*Pass & Seymour/Legrand*

Catalog Number	5362ISP
Manufacturer	Pass & Seymour/Legrand
Description	Surge Protective Extra Heavy-Duty Duplex Receptacle Offers Increased Transient Protection, Reliability and Protection Notification (Audible Alarm With Led Indicator). Back and, Side Wire, 20AMP 125VOLT, Ivory.
Weight per unit	0.3712 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and side wire
Material	Nylon
media	Yes
Number of Wires	3
Poles	2
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	#14 - #10

### Material, Color, and Finish

Color	Ivory
-------	-------

### Dimensions and Weight

Height	3.75
Width	1.25



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TVSS RECP 20A 125V ALARM IV
extra long description	P&S 5362ISP TVSS RECP 20A 125V ALAR
Long Description	Surge Protective Extra Heavy-Duty Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and, Side Wire, 20amp 125volt, Ivory.
Product Type	TVSS Recp 20A 125V Alarm Iv
Special Features	Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place. LED Indication: steady green = protected, flashing red = not protected, OFF = no power to unit. Audible alarm alert of MOV damage. Alarm able to be turned On/Off. Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation. Impact-resistant nylon exterior resists impacts and scrapes. Triple-wipe, copper-alloy contacts for superior, more dep

## Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007194388
Manufacturers Part Number	5362-ISP
UPC	785007194388

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Spec Grade Surge Protective Receptacle, Audible Alarm with LED Indicator

## Packaging

Carton	1
Package	50
Weight Per each	0.3712

## Uses, Certifications, and Standards

Application	Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
nema rating	5-20R
standard	ANSI/EEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).;CSA C22.2 No. 42;cUL UL1449, UL498
Temperature Rating	Operating Temperature: -20°C to +55°C (-4°F to 131°F), Storage Temperature: -40°C to +85°C (-40°F to 185°F)