



Powering Business Worldwide

5366N

Plug 20A 125V 2P3W Str AutoGrip BW

UPC: 040893018058

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Special Features: Wiring Type Back and Side Wire, Isolated Ground

Application: Hospital

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Thermoplastic/Nylon Top Housing, Glass Filled Nylon Bottom Housing

Color: Gray

NEMA Rating: 5-15R

Connection: Screw

5366NCR

Plug CR 20A 125V 2P3W Str AutoGrip YL

UPC: 040893018102

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Special Features: Wiring Type Back and Side Wire, Isolated Ground

Application: Hospital

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Thermoplastic/Nylon Top Housing, Glass Filled Nylon Bottom Housing

Color: Red

NEMA Rating: 5-15R

Connection: Screw



Powering Business Worldwide

5366NHG

Plug HG 20A 125V 2P3W Str AutoGrip BW

UPC: 040893018157

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 20 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, PVC Base

Color: Ivory

NEMA Rating: 5-20R

Connection: Screw



Powering Business Worldwide

5366N

Plug 20A 125V 2P3W Str AutoGrip BW

UPC: 040893018058

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Special Features: Wiring Type Back and Side Wire, Isolated Ground

Application: Hospital

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Thermoplastic/Nylon Top Housing, Glass Filled Nylon Bottom Housing

Color: Gray

NEMA Rating: 5-15R

Connection: Screw

5366NCR

Plug CR 20A 125V 2P3W Str AutoGrip YL

UPC: 040893018102

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Special Features: Wiring Type Back and Side Wire, Isolated Ground

Application: Hospital

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 15 Amp

Voltage Rating: 125 Vac

Material: Thermoplastic/Nylon Top Housing, Glass Filled Nylon Bottom Housing

Color: Red

NEMA Rating: 5-15R

Connection: Screw



Powering Business Worldwide

5366NHG

Plug HG 20A 125V 2P3W Str AutoGrip BW

UPC: 040893018157

Brand Name: Cooper Wiring Devices

Sub Brand: ARROW HART

Type: Duplex, Straight Blade

Number Of Poles: 2

Number Of Wires: 3

Wire Size: 14 To 10 AWG

Amperage Rating: 20 Amp

Voltage Rating: 125 Vac

Material: Nylon Face, PVC Base

Color: Ivory

NEMA Rating: 5-20R

Connection: Screw