



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



538722 1/2" Dual Speed Hammer-Drill Kit

Milwaukee Electric Tool

| | |
|------------------|--|
| Catalog Number | 538722 |
| Manufacturer | Milwaukee Electric Tool |
| Description | Choose The Hammer Drill With Power and Speed Controls For Unmatched Versatility. The Adaptable 1/2 In. Dual-Speed Hammer Drill Features An 8.5 Amp Motor That Provides Overload Protection, Even When Drilling 3/4 In. Holes In Concrete. Choose Controls In Two Ranges: 0-1, 000 RPM/0-16, 000 BPM or 0-2, 500 RPM/0-40, 000. It'S Versatile Enough to Drill In Wood With Flat Boring Bits, Hole Saws, Auger Bits and Selfeed Bits – or Drill In Steel With Twist Bits and In Concrete With Percussion Bits. The Removable Side |
| Weight per unit | 12.4 (lbs/each) |
| Product Category | Power Tools - Corded |

Features

| | |
|-----------------|-----|
| amperage rating | 8.5 |
|-----------------|-----|

Descriptions

| | |
|------------------------|--|
| Description | 1/2" DUAL SPEED HAMMER-DRILL KIT |
| extra long description | MILW 5387-22 1/2"8.5AHmnrDrillKit |
| Features | 1/2 in. Dual Speed Hammer Drill Kit w/ Case |
| Long Description | Choose the hammer drill with power and speed controls for unmatched versatility. The adaptable 1/2 in. dual-speed hammer drill features an 8.5 amp motor that provides overload protection, even when drilling 3/4 in. holes in concrete. Choose controls in two ranges: 0-1, 000 RPM/0-16,000 bpm or 0-2, 500 RPM/0-40,000. It's versatile enough to drill in wood with flat boring bits, hole saws, auger bits and Selfeed bits – or drill in steel with twist bits and in concrete with percussion bits. The removable side |
| Product Type | 1/2"8.5ahmnrdrillkit |
| Short Description | 1/2"85AHmnrDrillKt |
| Special Features | 8.5 AMP Motor Provides Overload Protection; Metal Gear Case Can Withstand Daily Jobsite Abuse; Light Weight Balanced Design Reduces Operator Fatigue; Dual Speed Motor Optimized For Concrete Fastening: 1-1,000 RPM, 0-16,000 BPM; 0-2,500 RPM, 0-40,000 BPM; Bpm: 0 - 16000/0 - 40000 BPM At No Load; Chuck Type: Keyed; Selfeed Bit Capacity: 2 IN; Cord Type: 10 FT Quik-Lok; Trigger Lock: No; Capacity In Steel: 1/2 IN; Capacity In Concrete: 3/4 IN; Tool Weight: 6.400 LB; Includes: Depth Gauge, Side Handle, Ch |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242025343 |
| Manufacturers Part Number | 538722 |
| UPC | 045242025343 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | POWER TOOLS |
| Type | Dual Speed |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 12.35 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | For Drilling In Wood With Flat Boring Bits, Hole Saws, Auger Bits, And Selffeed Bits, It Can Also Be Used To Drill In Steel With Twist Bits And In Concrete With Percussion Bits |
|-------------|--|