



**TWO GANG EXTENSION & THREE GANG BOX**

2-5/8 in. Deep with Lugs - Seven Threaded Outlets - 4-1/2 in. x 6-3/8 in.  
N/A

**D07.1**



Catalog #: 5390-0

**APPLICATIONS**

For use in branch circuit wiring in wet, damp, or dry locations  
May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

**PRODUCT FEATURES**

- Reinforced connector outlets
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Eight box mounting options with detachable lugs
- Four closure plugs included
- Hubs accept all threaded fittings and threaded conduit
- Ground screw installed
- Multi-lingual instructions in each package
- Includes gasket and mounting hardware
- N/A

**UL LISTED**

File E195978

**CSA**

C22.2 No. 18

**NEMA**

3R Rated

**GENERAL PRODUCT INFORMATION**

Color: Gray

**CONFIGURATION**

Number Of Outlets: 7  
Gangs: 3

**PRODUCT MEASUREMENTS**

Depth: 2-5/8 in.  
Outlet Size: 3/4 in.  
Cubic Inches (cm3): 55.0 (901.3)  
Wt. Ea. (Lbs.): 1.550

**PACKAGING**


Package Type: Boxed  
Std. Pkg.: 1  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 155.00  
Ship Carton Length (in.): 9.25  
Ship Carton Width (in.): 5.75  
Ship Carton Height (in.): 5.00  
Ctn Weight (Lbs.): 1.55  
Pallet Qty: 200.00  
UPC Number: 050169539002  
I2of5: 50050169539007



**TWO GANG EXTENSION & THREE GANG BOX**

2-5/8 in. Deep with Lugs - Seven Threaded Outlets - 4-1/2 in. x 6-3/8 in.  
N/A

**D07.1**



Catalog #: 5390-0

**APPLICATIONS**

For use in branch circuit wiring in wet, damp, or dry locations  
May be used as a weatherproof junction box, or as a housing for receptacles, switches, and GFCI's

**PRODUCT FEATURES**

- Reinforced connector outlets
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Eight box mounting options with detachable lugs
- Four closure plugs included
- Hubs accept all threaded fittings and threaded conduit
- Ground screw installed
- Multi-lingual instructions in each package
- Includes gasket and mounting hardware
- N/A

**UL LISTED**

File E195978

**CSA**

C22.2 No. 18

**NEMA**

3R Rated

**GENERAL PRODUCT INFORMATION**

Color: Gray

**CONFIGURATION**

Number Of Outlets: 7  
Gangs: 3

**PRODUCT MEASUREMENTS**

Depth: 2-5/8 in.  
Outlet Size: 3/4 in.  
Cubic Inches (cm3): 55.0 (901.3)  
Wt. Ea. (Lbs.): 1.550

**PACKAGING**

Package Type: Boxed  
Std. Pkg.: 1  
Product UPC-A Labeled: Yes  
Weight (Lbs. Per/C): 155.00  
Ship Carton Length (in.): 9.25  
Ship Carton Width (in.): 5.75  
Ship Carton Height (in.): 5.00  
Ctn Weight (Lbs.): 1.55  
Pallet Qty: 200.00  
UPC Number: 050169539002  
I2of5: 50050169539007