



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



54811 3/0 2WAY Cop Conn

Abb Installation Products, Inc

Catalog Number	54811
Manufacturer	Abb Installation Products, Inc
Description	Copper Two-Way Splice, Long Barrel, Max 354KV, Wire Size 3/0 Awg, Length 2.25 Inches, Diameter 0.65 Inch, Tin Plated, Die Code Orange, Die Color Code Orange
Weight per unit	0.0910 (lbs/each)
Product Category	Large Terminals & Connectors

Features

insulation	None
Material	Copper
Voltage Rating	600 V

Material, Color, and Finish

Color	Orange
Finish	Tin-Plated

Descriptions

Description	3/0 2WAY COP CONN
extra long description	ABB 54811 2WAY CU SPLICE CONN LNGBR
Long Description	Copper Two-Way Splice, Long Barrel, Max 354kV, Wire Size 3/0 AWG, Length 2.25 Inches, Diameter 0.65 Inch, Tin Plated, Die Code Orange, Die Color Code Orange
Product Type	2WAY Cu Splice Conn LNGBRL 3/0 Org
Special Features	Two-Way Connectors Provide High Pullout Values, are Easy to Insulate and Provide a Low-Resistance Connection of High Quality and Low Installed Cost

Manufacturer Information

Brand	COLOR-KEYED
GTIN	00786210548111
Manufacturers Part Number	54811
UPC	786210548111

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Splice Connector

Packaging

Carton	10
Package	100
Weight Per each	0.091



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Applications certified to 600 V and recommended up to 35 kV
standard	UL E9809, CSA 4503 / UL E9809, CSA 4503