ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

552020507 20/2 Thermostat Wire

Southwire Company

Catalog Number	552020507
Manufacturer	Southwire Company
Description	Thermostat Wire, Solid, 2 Conductors, #20 Awg Conductor Size, 150 V, 500 FT Overall Length, 0.114 In Outside Diameter, 0.006 In Insulation Thickness, Copper Conductor Material, Polyethylene (Xlpe) Insulation Material, Red;White, -20 °C Operating Temperature, +60 °C Operating Temperature, 9 LB/MFT
Weight per unit	0.0090 (lbs/ft)
Product Category	Jacketed Thermostat Wire & CBL

Descriptions

Description	20/2 THERMOSTAT WIRE
extra long description	SWC 552020507 TSTAT 20/2 CU CL2/CMH
Features	The Southwire 500 ft. Brown 18/2 Thermostat and Bell Cable is rated to 150-Volt and is classified as class-2 power-limited circuit cable. This thermostat and bell cable offers solid copper conductors with PVC insulation. This thermostat wire is also sunlight resistant.

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892351854
UPC	029892351854

Taxonomies, Classifications, and Categories

Category Description	Thermostat and Doorbell Wire

Availability

minimum qty	500

Packaging

Carton	500
Package	2000
Weight Per foot	0.009