


# Thermostat Cables



## 18 AWG SOL BC – Baro-Pak™ – Brown



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55302-55-07	2	13	1 x 500
55303-55-07	3	16	1 x 500
55304-54-07	4	28	1 x 250
55305-54-07	5	29	1 x 250
55306-54-07	6	35	1 x 250
55307-54-07	7	41	1 x 250
55308-54-07	8	47	1 x 250
55309-54-07	9	52	1 x 250
55310-54-07	10	54	1 x 250
55312-54-07	12	69	1 x 250

ETL Type CL2, CETL Listed Type CL2 or CMH/FT1, NEC Article 725, Put-up = 250' (54), 500' (55), Color Code: Brown (07)


## 20 AWG SOL BC – Baro-Pak™ – Brown



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55202-55-07	2	8	1 x 500
55203-55-07	3	10	1 x 500
55204-54-07	4	14	1 x 250
55205-54-07	5	17	1 x 250
55206-54-07	6	21	1 x 250
55207-54-07	7	24	1 x 250
55208-54-07	8	28	1 x 250
55209-54-07	9	32	1 x 250
55210-54-07	10	36	1 x 250
55212-54-07	12	46	1 x 250

ETL Type CL2, CETL Type CL2 or CMH/FT1, NEC Article 725, Put-up = 250' (54), 500' (55), Color Code: Brown (07)

## 18 AWG SOL BC BaroStat™ – Reels – Brown



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55302-05-07	2	14	4 x 500
55303-05-07	3	19	4 x 500
55304-04-07	4	25	4 x 250
55305-04-07	5	31	4 x 250
55306-04-07	6	37	4 x 250
55307-04-07	7	44	4 x 250
55308-04-07	8	50	4 x 250
55309-04-07	9	55	4 x 250
55310-04-07	10	61	4 x 250
55312-04-07	12	72	1 x 250

ETL Type CL2, CETL Type CL2 or CMH/FT1, NEC Article 725, Put-up = 250' (04), 500' (05), Color Code: Brown (07)

## 20 AWG SOL BC BaroStat™ – Reels – Brown



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55202-05-07	2	9	4 x 500
55203-05-07	3	12	4 x 500
55204-04-07	4	16	4 x 250
55205-04-07	5	19	4 x 250
55206-04-07	6	23	4 x 250
55207-04-07	7	26	4 x 250
55208-04-07	8	30	4 x 250
55209-04-07	9	34	4 x 250
55210-04-07	10	38	4 x 250
55212-04-07	12	46	4 x 250

ETL Type CL2, CETL Listed CL2 or CMH/FT1, NEC Article 725, Put-up = 250' (04), 500' (05), Color Code: Brown (07)

## 18 AWG SOL BC BaroStat™ – Reels – White



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55302-05-01	2	14	4 x 500
55303-05-01	3	19	4 x 500
55304-04-01	4	25	4 x 250
55305-04-01	5	31	4 x 250
55306-04-01	6	37	4 x 250
55307-04-01	7	44	4 x 250
55308-04-01	8	50	4 x 250
55309-04-01	9	55	4 x 250
55310-04-01	10	61	4 x 250

ETL Type CL2, CETL Type CL2 or CMH/FT1, NEC Article 725, Put-up = 250' (04), 500' (05), Color Code: White (01)



## 16 AWG SOL BC BaroStat™ – Reels


Part Number	No of Cond	Wt/ 1000'	Std Pkg
55403-05-07	3	31	1 X 500
55405-05-07	5	49	1 x 500
55406-05-07	6	58	1 x 500
55408-05-07	8	75	1 x 500
55410-05-07	10	98	1 x 500

ETL Type CL2, CETL Listed, Type CM/CL2 or CMM/FT1, NEC Article 725, Put-up = 250' (04), 500' (05), Color Code: Brown (07)

# Thermostat Cables



## 18 AWG SOL BC – Baro-Pak™ – Brown



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55302-55-07	2	13	1 x 500
55303-55-07	3	16	1 x 500
55304-54-07	4	28	1 x 250
55305-54-07	5	29	1 x 250
55306-54-07	6	35	1 x 250
55307-54-07	7	41	1 x 250
55308-54-07	8	47	1 x 250
55309-54-07	9	52	1 x 250
55310-54-07	10	54	1 x 250
55312-54-07	12	69	1 x 250

ETL Type CL2, CETL Listed Type CL2 or CMH/FT1,  
NEC Article 725, Put-up = 250' (54), 500' (55),  
Color Code: Brown (07)


## 20 AWG SOL BC – Baro-Pak™ – Brown



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55202-55-07	2	8	1 x 500
55203-55-07	3	10	1 x 500
55204-54-07	4	14	1 x 250
55205-54-07	5	17	1 x 250
55206-54-07	6	21	1 x 250
55207-54-07	7	24	1 x 250
55208-54-07	8	28	1 x 250
55209-54-07	9	32	1 x 250
55210-54-07	10	36	1 x 250
55212-54-07	12	46	1 x 250

ETL Type CL2, CETL Type CL2 or CMH/FT1,  
NEC Article 725, Put-up = 250' (54), 500' (55),  
Color Code: Brown (07)

## 18 AWG SOL BC BaroStat™ – Reels – Brown



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55302-05-07	2	14	4 x 500
55303-05-07	3	19	4 x 500
55304-04-07	4	25	4 x 250
55305-04-07	5	31	4 x 250
55306-04-07	6	37	4 x 250
55307-04-07	7	44	4 x 250
55308-04-07	8	50	4 x 250
55309-04-07	9	55	4 x 250
55310-04-07	10	61	4 x 250
55312-04-07	12	72	1 x 250

ETL Type CL2, CETL Type CL2 or CMH/FT1, NEC Article 725,  
Put-up = 250' (04), 500' (05), Color Code: Brown (07)

## 20 AWG SOL BC BaroStat™ – Reels – Brown



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55202-05-07	2	9	4 x 500
55203-05-07	3	12	4 x 500
55204-04-07	4	16	4 x 250
55205-04-07	5	19	4 x 250
55206-04-07	6	23	4 x 250
55207-04-07	7	26	4 x 250
55208-04-07	8	30	4 x 250
55209-04-07	9	34	4 x 250
55210-04-07	10	38	4 x 250
55212-04-07	12	46	4 x 250

ETL Type CL2, CETL Listed CL2 or CMH/FT1,  
NEC Article 725, Put-up = 250' (04), 500' (05)  
Color Code: Brown (07)

## 18 AWG SOL BC BaroStat™ – Reels – White



Part Number	No of Cond	Wt/ 1000'	Std Pkg
55302-05-01	2	14	4 x 500
55303-05-01	3	19	4 x 500
55304-04-01	4	25	4 x 250
55305-04-01	5	31	4 x 250
55306-04-01	6	37	4 x 250
55307-04-01	7	44	4 x 250
55308-04-01	8	50	4 x 250
55309-04-01	9	55	4 x 250
55310-04-01	10	61	4 x 250

ETL Type CL2, CETL Type CL2 or CMH/FT1, NEC Article 725,  
Put-up = 250' (04), 500' (05), Color Code: White (01)



## 16 AWG SOL BC BaroStat™ – Reels

Part Number	No of Cond	Wt/ 1000'	Std Pkg
55403-05-07	3	31	1 X 500
55405-05-07	5	49	1 x 500
55406-05-07	6	58	1 x 500
55408-05-07	8	75	1 x 500
55410-05-07	10	98	1 x 500

ETL Type CL2, CETL Listed, Type CM/CL2 or CMM/FT1,  
NEC Article 725, Put-up = 250' (04), 500' (05),  
Color Code: Brown (07)