

Modular jacks & adapters

Product description

Voice, data, Category 3 RJ11, Category 6 RJ45, Category 5E RJ45, RG6 F-Type coax

Design features

- 110 style modular jacks
- Data jacks have 8 positions and 8 conductors for high-speed LAN applications
- Category 3 jacks have 6 positions and 6 conductors for voice and/or data applications
- Category 6 jacks are rated for 650MHz, Category 5E jacks are rated for 160MHz
- IDC termination for simple and fast installation
- Color coding wiring labels for both T568A/B and USOC helps easy selection of products
- Video connectors require no soldering
- All jacks and adapters clip smoothly into place in our flush-mount modular wallplates providing ease of installation



5546-6



5547-5E



5547-3E



5552-5E




5550-5E

Modular jacks & adapters

| Description | Features | Color suffix | Catalog no. | |
|------------------------------|--|--------------|-------------|---|
| Data jack, category 6 RJ45 | 8-position, 8-conductor 568A/B wiring | LA, V, W | □ 5546-6__ | • |
| Data jack, category 5e RJ45 | 8-position, 8-conductor 568A/B wiring | BL, LA, V, W | □ 5547-5E__ | • |
| Voice jack, category 3 RJ11 | 6-position, 6-conductor USDOC wiring | LA, V, W | □ 5547-3E__ | • |
| Video connector, F-type coax | For RG6 applications TV/satellite | LA, V, W | □ 5552-5E__ | • |
| Blank insert | For filling empty ports/solid blank face | LA, V, W | □ 5550-5E__ | • |

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: BL (Blue), LA (Light Almond), V (Ivory), W (White)



Specification information: Please visit www.eaton.com/wiringdevices

Compliances, specifications and availability are subject to change without notice.

RoHS compliant

Modular jacks & adapters

Product description

Voice, data, Category 3 RJ11, Category 6 RJ45, Category 5E RJ45, RG6 F-Type coax

Design features

- 110 style modular jacks
- Data jacks have 8 positions and 8 conductors for high-speed LAN applications
- Category 3 jacks have 6 positions and 6 conductors for voice and/or data applications
- Category 6 jacks are rated for 650MHz, Category 5E jacks are rated for 160MHz
- IDC termination for simple and fast installation
- Color coding wiring labels for both T568A/B and USOC helps easy selection of products
- Video connectors require no soldering
- All jacks and adapters clip smoothly into place in our flush-mount modular wallplates providing ease of installation



5546-6



5547-5E



5547-3E



5552-5E




5550-5E

Modular jacks & adapters

| Description | Features | Color suffix | Catalog no. | |
|------------------------------|---|--------------|-------------|---|
| Data jack, category 6 RJ45 | 8-position, 8-conductor 568A/B wiring | LA, V, W | □ 5546-6__ | • |
| Data jack, category 5e RJ45 | 8-position, 8-conductor 568A/B wiring | BL, LA, V, W | □ 5547-5E__ | • |
| Voice jack, category 3 RJ11 | 6-position, 6-conductor USDOC wiring | LA, V, W | □ 5547-3E__ | • |
| Video connector, F-type coax | For RG6 applications TV/satellite | LA, V, W | □ 5552-5E__ | • |
| Blank insert | For filling empty portssolid blank face | LA, V, W | □ 5550-5E__ | • |

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: BL (Blue), LA (Light Almond), V (Ivory), W (White)



Specification information: Please visit www.eaton.com/wiringdevices

Compliances, specifications and availability are subject to change without notice.

RoHS compliant