



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5651I SGL Recp 15A 250V S-Wire Iv *Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | 5651I  |
| Manufacturer     | Pass & Seymour/Legrand                                     |
| Description      | Heavy-Duty Spec Grade Single Receptacle Side Wire 15A 250V |
| Weight per unit  | 0.1636 (lbs/each)  |
| Product Category | Gen Purpose Recept & Surge Pro                             |

### Features

|                     |  |
|---------------------|--|
| amperage rating     | 15   |
| connection          | Back and side wire                               |
| Dielectric Strength | Withstands 2000V minimum                         |
| indoor/outdoor      | Indoor   |
| Material            | Nylon  |
| Number of Wires     | 3  |
| Outlet Type         | Indoor, Commercial                               |
| Poles               | Double Pole                                      |
| Voltage             | 250.0 V  |
| Voltage Rating      | 250  |
| Wattage             | Electrical power is expressed in Amps and Volts. |
| Wire Size           | 14 - 10  |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | Ivory |
| Finish | Matte |

### Dimensions and Weight

|        |      |
|--------|------|
| Height | 3.68 |
| Width  | 1.08 |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | SGL RECP 15A 250V S-WIRE IV   |
| extra long description | P&S 5651I RECP SGL 15A 250V S-WIRE  |
| Long Description       | Heavy-Duty Spec Grade Single Receptacle Side Wire 15A 250V  |
| Product Type           | Recp SGL 15A 250V S-Wire Iv   |
| Special Features       | Auto-ground clip assures positive ground. Two drive screws anchor strap to back body and face where abrupt removal torque is greatest. Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength. Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility. One-piece brass triple-wire power contacts for lasting retention. |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Pass & Seymour |
| GTIN                      | 00785007565119 |
| Manufacturers Part Number | 5651-I         |
| UPC                       | 785007565119   |

## Taxonomies, Classifications, and Categories

|                      |                        |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type                 | Outlet                 |

## Trade Size

|          |      |
|----------|------|
| Amperage | 15.0 |
|----------|------|

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Package         | 100    |
| Weight Per each | 0.1636 |

## Uses, Certifications, and Standards

|                          |                                |
|--------------------------|--------------------------------|
| Application              | Commercial                     |
| environmental conditions | Flammability: UL94 V2          |
| Mounting                 | WALL                           |
| nema rating              | 6-15R                          |
| standard                 | CULUS, UL498, CSA C22.2 No. 42 |
| Temperature Rating       | -40° - 60° C                   |