



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



570GI 3/8" GRN Insld HCF CBL Conn *Bridgeport Fittings*

| | |
|------------------|--------------------------------|
| Catalog Number | 570GI |
| Manufacturer | Bridgeport Fittings |
| Description | HCF Cable Connector |
| Weight per unit | 0.0700 (lbs/each) |
| Product Category | BX, MC, Armored Cable Fittings |

Features

| | |
|----------------------|---------------|
| angle | 180 Deg |
| Connector Type | Color-Coded |
| Material | Zinc Die Cast |
| media | Yes |
| Number of Conductors | 1 Cable |

Material, Color, and Finish

| | |
|--------|---------------|
| Color | Green |
| Finish | Green Colored |

Dimensions and Weight

| | |
|------|-----|
| Size | 3/8 |
|------|-----|

Descriptions

| | |
|------------------------|--|
| Description | 3/8" GRN INSLTD HCF CBL CONN |
| extra long description | BPT 570-GI 3/8" GREEN INS HCF CABLE |
| Features | Think Bridgeport: Color Coded GREEN for Hospital Care Facilities requiring cable run identification. |
| Long Description | HCF Cable Connector |
| Product Type | 3/8" Green Ins HCF Cable Conn |
| Special Features | Hcf/Hcfmci-A |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747757067 |
| Manufacturers Part Number | 570-GI |
| UPC | 781747757067 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | FORM 7, 8, CONDULETS, COVERS, & GASKETS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-----|
| Trade Size | 3/8 |
|------------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 50 |
| Package | 500 |
| Weight Per each | 0.07 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| Application | Recommended cable types for use with Steel or Aluminum 14/2 (.38" 0 min) to 10/3 AWG (.61" 0 max) Health Care Facility (HCF) Armored Cable. AC/MC/MCI-A |
| standard | UL |
| Temperature Rating | 105°C |