

Bar Hangers and Brackets



BCBK-01



BCBK-20



6010DW-25 / 6010ADW-25



6011DW-25 / 6011ADW-25



CI1060



| Cat. No. | Description |
|--------------------|----------------------------------------------------------------------------------------------------------------------|
| Bar Hangers | |
| BCBK-01 | Adjustable hanger for wood stud. Length: 15.5 in. Height: 2.5 in. |
| BCBK-20 | Adjustable hanger for octagonal boxes for furring channel. Width: 4-1/2 in. x Height: 1-3/8 in. x Length: 21-1/8 in. |
| CI1060 | Length: 16 in. Grooved for box ears |



| Cat. No. | Description | Maximum load capacity | Length |
|------------------------------------------------------------------------------------|------------------------------------------------------------------------------|-----------------------|----------------------|
| Adjustable bar hangers for 3/8 in., 1/2 in. and 5/8 in. drywall and plaster | | | |
| 6010DW-25 | Score marks for drywall and plaster depths. Packaged complete with stud. | 50 lb. (22.7 kg) | 10-1/2 in. to 18 in. |
| 6010ADW-25 | | | 14-1/2 in. to 25 in. |
| 6011DW-25 | Score marks for drywall and plaster depths. Packaged complete with fastener. | | 10-1/2 in. to 18 in. |
| 6011ADW-25 | | | 14-1/2 in. to 25 in. |

* These products replace Iberville® BC1041 and BC1042 bar hangers.

Bar Hangers and Brackets

Extra heavy-duty new work bar hanger Ceiling fan and light fixture bar hanger

This innovative extruded-aluminum bar hanger was designed for strength. It is cULus Listed for up to 70 lb. for fan support and an industry-leading 200 lb. for fixture support.

- Gold Glav-Krom™ finish on mounting screws easily identifies hanger as meeting CEC & cULus requirements for fan or light fixture
- Screwed-on end plates are consistently strong and avoid unsightly welds
- End plates feature temporary fixing spikes for hands-free installation
- Expandable for joints spaced from 14.5 to 24 in.



| Cat. No. | Description | Volume (Cu. in.) |
|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------|
| 54151CFB-NW | New work bar hanger with 4 in. octagonal 1-1/2 in. deep box with NMD90 cable clamps. (wood screws included) Maximum load capacity: Fan 70 lb. and fixture 200 lb. | 15.8 |

Bar Hangers and Brackets

Extra heavy-duty rework bar hanger

Ceiling fan and light fixture bar hanger

Exhaustive research and development has resulted in an innovative of ceiling fan support boxes that give Thomas & Betts the competitive advantage. Ceiling fan and fixture installation is faster, easier and safer with Steel City® ceiling fan support boxes.

- Gold Glav-Krom™ finish on mounting screws easily identifies hanger as meeting CEC & cULus requirements for fan or light fixture
- cULus Listed up to 70 lb. for fan and 200 lb. for light fixture
- Square end plates keep the bar parrallel with sheetrock
- Expandable for joints from 14.5 to 24 in.



| Cat. No. | Description | Volume (Cu. in.) |
|-------------|------------------------------------------------------------------------------------------------------------------------------------------|------------------|
| 54151CFB-0W | Rework bar hanger with 4 in. octagonal 1-1/2 in. deep box with NMD90 cable clamps. Maximum load capacity: Fan 70 lb. and fixture 200 lb. | 15.8 |