


CONDUIT HANGERS



| CAT# | A | B | C | D |
|-----------|-------|-------|-------|-------|
| 611/601 | 1.875 | .750 | .725 | .25 |
| 612/602 | 2.125 | .750 | .850 | .25 |
| 613/603 | 2.437 | .875 | .975 | .25 |
| 614/604 | 2.75 | .875 | .975 | .25 |
| 614A/604A | 2.875 | .875 | 1.050 | .25 |
| 615/605 | 3.125 | 1.000 | 1.125 | .25 |
| 616/606 | 3.875 | 1.000 | 1.145 | .25 |
| 617/607 | 4.625 | 1.250 | 1.225 | .3125 |
| 618/608 | 5.500 | 1.250 | 1.275 | .3125 |
| 619/609 | 5.750 | 1.250 | 1.275 | .3125 |
| 620/610 | 6.250 | 1.250 | 1.275 | .3125 |

STEEL

| TOPAZ CAT # | UPC# | TRADE SIZE | FOR RIGID | FOR EMT | BOLT SIZE | SHIP CASE | WT/ CASE |
|---------------------------------------|-------|------------|-----------|---------|-----------|-----------|----------|
| WITH BOLTS & NUTS ATTACHED | | | | | | | |
| 601 | 15830 | 0 | 3/8"-1/2" | 1/2" | 1/4-20 | 100 | 6 |
| 602 | 15840 | 1 | 3/4" | 3/4" | 1/4-20 | 100 | 8 |
| 603 | 15850 | 2 | 1" | 1" | 1/4-20 | 100 | 8 |
| 604 | 15860 | 3 | 1 1/4" | 1 1/2" | 1/4-20 | 100 | 10 |
| 604A | 15870 | 2 1/2 | --- | 1 1/4" | 1/2-20 | 100 | 10 |
| 605 | 15880 | 4 | 1 1/2" | --- | 1/2-20 | 100 | 18 |
| 606 | 15890 | 5 | 2" | 2" | 1/2-20 | 50 | 10 |
| 607 | 15900 | 6 | 2 1/2" | 2 1/2" | 5/16-18 | 50 | 11 |
| 608 | 15910 | 7 | 3" | 3" | 5/16-18 | 25 | 6 |
| 609 | 15920 | 8 | 3 1/2" | 3 1/2" | 5/16-18 | 25 | 8 |
| 610 | 15930 | 9 | 4" | 4" | 5/16-18 | 25 | 12 |



E174011

WITHOUT BOLTS & NUTS

| | | | | | | | |
|------|-------|-------|-----------|--------|-----|-----|----|
| 611 | 15940 | 0 | 3/8"-1/2" | 1/2" | --- | 100 | 5 |
| 612 | 15950 | 1 | 3/4" | 3/4" | --- | 100 | 7 |
| 613 | 15960 | 2 | 1" | 1" | --- | 100 | 7 |
| 614 | 15970 | 3 | 1 1/4" | 1 1/2" | --- | 100 | 9 |
| 614A | 15980 | 2 1/2 | --- | 1 1/4" | --- | 100 | 9 |
| 615 | 15990 | 4 | 1 1/2" | --- | --- | 100 | 17 |
| 616 | 16000 | 5 | 2" | 2" | --- | 50 | 9 |
| 617 | 16010 | 6 | 2 1/2" | 2 1/2" | --- | 50 | 11 |
| 618 | 16020 | 7 | 3" | 3" | --- | 25 | 5 |
| 619 | 16030 | 8 | 3 1/2" | 3 1/2" | --- | 25 | 7 |
| 620 | 16040 | 9 | 4" | 4" | --- | 25 | 11 |



E174011





FLUORESCENT CHAIN

| CAT# | WORKLOAD LIMITS |
|------|-----------------|
| FC1 | 50 LBS. |

STEEL

| TOPAZ CAT # | UPC# | SIZE | UNIT CTN | SHIP CASE | WT/ CASE |
|-------------|-------|----------------|----------|-----------|----------|
| FC1 | 20750 | 1 YARD LENGTHS | 1 YD. | 100 | 35 |



JACK CHAIN

| CAT# | WORKLOAD LIMITS |
|------|-----------------|
| 297 | 16 LBS. |
| 298 | 29 LBS. |
| 298S | 29 LBS. |
| 299 | 29 LBS. |
| 299B | 43 LBS. |


• ZINC PLATED

STEEL

| TOPAZ CAT # | UPC# | SIZE | UNIT CTN | SHIP CASE | WT/ CASE |
|-------------|-------|---------------------|---------------|-----------|----------|
| 297 | 12480 | 14 GAUGE - LIGHT | 100 FT.HANKS | 10 | 50 |
| 298 | 12490 | 12 GAUGE - STANDARD | 50 FT.HANKS | 10 | 30 |
| 298S | 12500 | 12 GAUGE - STANDARD | 100 FT.SPOOLS | 4 | 48 |
| 299 | 12501 | 12 GAUGE - STANDARD | 250 FT.SPOOLS | 4 | 60 |
| 299B | 12505 | 10 GAUGE - HEAVY | 100 FT.HANKS | 1 | 18 |



CONDUIT HANGERS



| CAT# | A | B | C | D |
|-----------|-------|-------|-------|-------|
| 611/601 | 1.875 | .750 | .725 | .25 |
| 612/602 | 2.125 | .750 | .850 | .25 |
| 613/603 | 2.437 | .875 | .975 | .25 |
| 614/604 | 2.75 | .875 | .975 | .25 |
| 614A/604A | 2.875 | .875 | 1.050 | .25 |
| 615/605 | 3.125 | 1.000 | 1.125 | .25 |
| 616/606 | 3.875 | 1.000 | 1.145 | .25 |
| 617/607 | 4.625 | 1.250 | 1.225 | .3125 |
| 618/608 | 5.500 | 1.250 | 1.275 | .3125 |
| 619/609 | 5.750 | 1.250 | 1.275 | .3125 |
| 620/610 | 6.250 | 1.250 | 1.275 | .3125 |

| STEEL | | | | | | | |
|---------------------------------------|-------|------------|-----------|---------|-----------|-----------|----------|
| TOPAZ CAT # | UPC# | TRADE SIZE | FOR RIGID | FOR EMT | BOLT SIZE | SHIP CASE | WT/ CASE |
| WITH BOLTS & NUTS ATTACHED | | | | | | | |
| 601 | 15830 | 0 | 3/8"-1/2" | 1/2" | 1/4-20 | 100 | 6 |
| 602 | 15840 | 1 | 3/4" | 3/4" | 1/4-20 | 100 | 8 |
| 603 | 15850 | 2 | 1" | 1" | 1/4-20 | 100 | 8 |
| 604 | 15860 | 3 | 1 1/4" | 1 1/2" | 1/4-20 | 100 | 10 |
| 604A | 15870 | 2 1/2 | --- | 1 1/4" | 1/2-20 | 100 | 10 |
| 605 | 15880 | 4 | 1 1/2" | --- | 1/2-20 | 100 | 18 |
| 606 | 15890 | 5 | 2" | 2" | 1/2-20 | 50 | 10 |
| 607 | 15900 | 6 | 2 1/2" | 2 1/2" | 5/16-18 | 50 | 11 |
| 608 | 15910 | 7 | 3" | 3" | 5/16-18 | 25 | 6 |
| 609 | 15920 | 8 | 3 1/2" | 3 1/2" | 5/16-18 | 25 | 8 |
| 610 | 15930 | 9 | 4" | 4" | 5/16-18 | 25 | 12 |



E174011

WITHOUT BOLTS & NUTS

| | | | | | | | |
|------|-------|-------|-----------|--------|-----|-----|----|
| 611 | 15940 | 0 | 3/8"-1/2" | 1/2" | --- | 100 | 5 |
| 612 | 15950 | 1 | 3/4" | 3/4" | --- | 100 | 7 |
| 613 | 15960 | 2 | 1" | 1" | --- | 100 | 7 |
| 614 | 15970 | 3 | 1 1/4" | 1 1/2" | --- | 100 | 9 |
| 614A | 15980 | 2 1/2 | --- | 1 1/4" | --- | 100 | 9 |
| 615 | 15990 | 4 | 1 1/2" | --- | --- | 100 | 17 |
| 616 | 16000 | 5 | 2" | 2" | --- | 50 | 9 |
| 617 | 16010 | 6 | 2 1/2" | 2 1/2" | --- | 50 | 11 |
| 618 | 16020 | 7 | 3" | 3" | --- | 25 | 5 |
| 619 | 16030 | 8 | 3 1/2" | 3 1/2" | --- | 25 | 7 |
| 620 | 16040 | 9 | 4" | 4" | --- | 25 | 11 |




E174011



FLUORESCENT CHAIN

| CAT# | WORKLOAD LIMITS |
|------|-----------------|
| FC1 | 50 LBS. |

| STEEL | | | | | | |
|-------------|-------|----------------|----------|-----------|----------|--|
| TOPAZ CAT # | UPC# | SIZE | UNIT CTN | SHIP CASE | WT/ CASE | |
| FC1 | 20750 | 1 YARD LENGTHS | 1 YD. | 100 | 35 | |



JACK CHAIN

| CAT# | WORKLOAD LIMITS |
|------|-----------------|
| 297 | 16 LBS. |
| 298 | 29 LBS. |
| 298S | 29 LBS. |
| 299 | 29 LBS. |
| 299B | 43 LBS. |

• ZINC PLATED

| STEEL | | | | | | |
|-------------|-------|---------------------|---------------|-----------|----------|--|
| TOPAZ CAT # | UPC# | SIZE | UNIT CTN | SHIP CASE | WT/ CASE | |
| 297 | 12480 | 14 GAUGE - LIGHT | 100 FT.HANKS | 10 | 50 | |
| 298 | 12490 | 12 GAUGE - STANDARD | 50 FT.HANKS | 10 | 30 | |
| 298S | 12500 | 12 GAUGE - STANDARD | 100 FT.SPOOLS | 4 | 48 | |
| 299 | 12501 | 12 GAUGE - STANDARD | 250 FT.SPOOLS | 4 | 60 | |
| 299B | 12505 | 10 GAUGE - HEAVY | 100 FT.HANKS | 1 | 18 | |

