



Product Number: 13442

Order Abbreviation: 60B10/BL/2PK 120V

General Description: Incandescent B10 Décor Bulb Shape Clear Finish Medium Aluminum Base 60Watt 120Volt Blister Pack 12Bulbs Per Case 2Bulbs Per Package

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	60B10BL2PK 120V 12/CS 2/SKU
Average Rated Life (hr)	1500
Base	Medium
Bulb	B10
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	1.250
Diameter (mm)	31.75
Filament	C-7A
Lamp Finish	Clear
Maximum Overall Length - MOL (in)	3.813
Maximum Overall Length - MOL (mm)	96.8375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	60.00





Product Number: 13442

Order Abbreviation: 60B10/BL/2PK 120V

General Description: Incandescent B10 Décor Bulb Shape Clear Finish Medium Aluminum Base 60Watt 120Volt Blister Pack 12Bulbs Per Case 2Bulbs Per Package

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	60B10BL2PK 120V 12/CS 2/SKU
Average Rated Life (hr)	1500
Base	Medium
Bulb	B10
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	1.250
Diameter (mm)	31.75
Filament	C-7A
Lamp Finish	Clear
Maximum Overall Length - MOL (in)	3.813
Maximum Overall Length - MOL (mm)	96.8375
Nominal Voltage (V)	120.00
Nominal Wattage (W)	60.00



ECOLOGIC
TM

