



G16 1/2



G25



G40

Watts	Bulb	Base	Order Code	Description	Volts	Pkg. Qty.	Apprx. Hours	Filament	Length (in.)
Complexion or Vanity — 2" Diameter - Boxed									
15	G16 1/2	Cand	17698	15G161/2/W/BX	130	25	3000	C-7A	3
			17697	15G161/2/CL/BX	130	25	3000	C-7A	3
25	G16 1/2	Cand	60463	25G161/2/W/BX	130	25	3000	C-7A	3
			60462	25G161/2/CL/BX	130	25	3000	C-7A	3
40	G16 1/2	Cand	60465	40G161/2/W/BX	130	25	3000	C-7A	3
			60464	40G161/2/CL/BX	130	25	3000	C-7A	3
60	G16 1/2	Cand	60520	60G161/2/W/BX	130	25	3000	C-7A	3
			60466	60G161/2/CL/BX	130	25	3000	C-7A	3
Complexion or Vanity — 2" Diameter - Carded									
25	G16 1/2	Cand	60905	25G161/2/W (2/CD)	130	12 cds	3000	C-7A	3
			60904	25G161/2/CL (2/CD)	130	12 cds	3000	C-7A	3
40	G16 1/2	Cand	60907	40G161/2/W (2/CD)	130	12 cds	3000	C-7A	3
			60906	40G161/2/CL (2/CD)	130	12 cds	3000	C-7A	3
Mini Globe Bulb — 3" Diameter									
25	G25	Med	60966	25G25/CL	130	60	5000	C-9	4 7/16
			60967	25G25/W	130	60	5000	C-9	4 7/16
40	G25	Med	61002	40G25/CL	120	60	1500	C-9	4 7/16
			60968	40G25/CL	130	60	5000	C-9	4 7/16
			61003	40G25/W	120	60	1500	C-9	4 7/16
			60969	40G25/W	130	60	5000	C-9	4 7/16
			60970	40G25/W/3PK	130	20 pks	5000	C-9	4 7/16
60	G25	Med	61004	60G25/CL	120	60	1500	C-9	4 7/16
			60971	60G25/CL	130	60	5000	C-9	4 7/16
			61005	60G25/W	120	60	1500	C-9	4 7/16
			60972	60G25/W	130	60	5000	C-9	4 7/16
			60973	60G25/W/3PK	130	20 pks	5000	C-9	4 7/16
Globe Bulb — 5" Diameter									
40	G40	Med	61010	40G40/CL	130	24	5000	C-9	6 15/16
			61011	40G40/W	130	24	5000	C-9	6 15/16
60	G40	Med	61012	60G40/CL	130	24	5000	C-9	6 15/16
			61013	60G40/W	130	24	5000	C-9	6 15/16
100	G40	Med	61014	100G40/CL	130	24	5000	C-9	6 15/16
			61015	100G40/W	130	24	5000	C-9	6 15/16
150	G40	Med	61016	150G40/CL	130	24	5000	C-9	6 15/16
			61017	150G40/W	130	24	5000	C-9	6 15/16