

NEW!  
More on  
reverse

# Low Profile IN and OUT™ Cover

Low Profile when not in use • Extra Duty Weatherproof in use Cover

IN for  
GOOD LOOKS!



OUT  
to PLUG IN



Paintable  
White Cover  
VERTICAL  
Standard size  
60VV

TO CLOSE  
Bow out the  
sides of the extended  
cover and Push IN



Arlington's non-metallic **IN** and **OUT™** **Cover** is a low profile cover when *not in use*, and a deep, extra duty weatherproof in use cover when a cord's plugged in!

**IN**, cord holes seal the box to keep bugs out. It extends quickly and easily into the **OUT** position to accommodate a plug – then back to a low profile cover when closed.

- Covers fit over any box or opening in new or existing projects - *Cover is removable for easier device installation*
- **Two sizes** in Vertical and horizontal styles  
**60 series** fits over standard openings.  
**61 series** with installed oversized base, covers large openings or a round 3.5" outlet box.
- **Cover colors** Paintable white or clear
- Installed gaskets
- UV rated plastic for long outdoor life
- Listed weatherproof in use installation – Meets NEC Section 406.9 (B), for the protection of exterior outlets where an extra duty weatherproof in use cover is required for 15 or 20 AMP receptacles installed outdoors

Patented  
Additional patents pending



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717 • Fax 570/562.0646  
www.aifittings.com

# Vertical and Horizontal IN and OUT™ Cover

*Fits over All Boxes and Openings in New or Old Work*



**Fast, Easy Installation**

- 1 Feed device through opening.  
\* cover is removable for easier access




- 2 Install wiring device per manufacturer's instructions, and Local and National Electrical Codes using the pre-drilled holes in the base.




- 3 Install the plate and the installation is done!

## IN and OUT Covers for Standard Boxes



## for Oversized Openings or 3.5" Round Boxes



Catalog Number	UPC/DEI/NAED Mfg. #018997	Cover Orientation/Color <b>IN and OUT COVER</b>	Base Size	Unit Pkg	Std Pkg
60VW	00680	Vertical • White	Standard	1	4
61VW	00681	Vertical • White	Oversized	1	4
60VC	00682	Vertical • Clear	Standard	1	4
61VC	00683	Vertical • Clear	Oversized	1	4
60HW	00684	Horizontal • White	Standard	1	4
61HW	00685	Horizontal • White	Oversized	1	4
60HC	00686	Horizontal • Clear	Standard	1	4
61HC	00687	Horizontal • Clear	Oversized	1	4

Includes low profile cover, (1) standard duplex and (1) standard GFCI face plate, installation screws, installed gaskets

**IN and OUT Covers**  
**Meet NEC Section 406.9 (B)**  
for the protection of exterior outlets where an extra duty weatherproof in use cover is required for 15 or 20 AMP receptacles installed outdoors.



Distributed by



**Arlington**™

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717 • Fax 570/562.0646  
www.aifittings.com

Patented. Additional patents pending

IN&OUT COVER 0806 REV 1008, 0325/7500

NEW!  
More on  
reverse

# Low Profile IN and OUT™ Cover

Low Profile when not in use • Extra Duty Weatherproof in use Cover

IN for  
GOOD LOOKS!



OUT  
to PLUG IN



Paintable  
White Cover  
VERTICAL  
Standard size  
60VV

TO CLOSE  
Bow out the  
sides of the extended  
cover and Push IN



Arlington's non-metallic **IN** and **OUT™** **Cover** is a low profile cover when *not in use*, and a deep, extra duty weatherproof in use cover when a cord's plugged in!

**IN**, cord holes seal the box to keep bugs out. It extends quickly and easily into the **OUT** position to accommodate a plug – then back to a low profile cover when closed.

- Covers fit over any box or opening in new or existing projects - *Cover is removable for easier device installation*
- **Two sizes** in Vertical and horizontal styles  
**60 series** fits over standard openings.  
**61 series** with installed oversized base, covers large openings or a round 3.5" outlet box.
- **Cover colors** Paintable white or clear
- Installed gaskets
- UV rated plastic for long outdoor life
- Listed weatherproof in use installation – Meets NEC Section 406.9 (B), for the protection of exterior outlets where an extra duty weatherproof in use cover is required for 15 or 20 AMP receptacles installed outdoors

Patented  
Additional patents pending



**Arlington®**

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717 • Fax 570/562.0646  
www.aifittings.com

# Vertical and Horizontal IN and OUT™ Cover

*Fits over All Boxes and Openings in New or Old Work*



### Fast, Easy Installation

- 1 Feed device through opening.  
\* cover is removable for easier access




- 2 Install wiring device per manufacturer's instructions, and Local and National Electrical Codes using the pre-drilled holes in the base.



- 3 Install the plate and the installation is done!

### IN and OUT Covers for Standard Boxes



### for Oversized Openings or 3.5" Round Boxes

Horizontal  
61HW  
not shown



Catalog Number	UPC/DEI/NAED Mfg. #018997	Cover Orientation/Color <b>IN and OUT COVER</b>	Base Size	Unit Pkg	Std Pkg
60VW	00680	Vertical • White	Standard	1	4
61VW	00681	Vertical • White	Oversized	1	4
60VC	00682	Vertical • Clear	Standard	1	4
61VC	00683	Vertical • Clear	Oversized	1	4
60HW	00684	Horizontal • White	Standard	1	4
61HW	00685	Horizontal • White	Oversized	1	4
60HC	00686	Horizontal • Clear	Standard	1	4
61HC	00687	Horizontal • Clear	Oversized	1	4

Includes low profile cover, (1) standard duplex and (1) standard GFCI face plate, installation screws, installed gaskets

**IN and OUT Covers**  
**Meet NEC Section 406.9 (B)**  
for the protection of exterior outlets where an extra duty weatherproof in use cover is required for 15 or 20 AMP receptacles installed outdoors.



Distributed by



**Arlington**™

1 Stauffer Industrial Park  
Scranton, PA 18517  
800/233.4717 • Fax 570/562.0646  
www.aifittings.com

Patented. Additional patents pending

IN&OUT COVER 0806 REV 1008, 0325/7500