



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 61521 3-Phase/Motor Rotation Tester

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 61521   |
| Manufacturer     | Ideal   |
| Description      | 3-Phase/Motor Rotation Tester, Voltage Rating: 100 - 600 Vac (10 - 400 HZ) Nominal For Phase Presence Indication, Amperage Rating: 18 Milamp Maximum Consumption, 3 PH Phase, Temperature Rating: 5 - 131 Deg F Operating, -4 to 158 Deg F Storage, Display: Neon Lamps and Leds, Dimensions: 6 In Height X 2.8 In Width X 1.4 In Depth, Phase Rotary Field Direction: 1 - 600 Vac (2 - 400 HZ), Determination Of Motor Rotation: 1 - 600 Vac (2 - 400 HZ) Requires Greater Than 1/2 Turn, Over Load Protection: 550 V (Between |
| Weight per unit  | 1.1 (lbs/each)  |
| Product Category | Testers & Accessories   |

### Features

|                 |   |
|-----------------|---|
| amperage rating | 18 MILAMP Maximum Consumption                                     |
| dimensions      | 6 IN Height X 2.8 IN Width X 1.4 IN Depth                         |
| display         | Neon Lamps And LEDs   |
| Phase           | 3 Ph  |
| Voltage Rating  | 100 - 600 VAC (10 - 400 HZ) Nominal For Phase Presence Indication |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 3-PHASE/MOTOR ROTATION TESTER   |
| extra long description | IDEAL 61-521 3 PHASE MOTOR ROTATION   |
| Features               | Identifies three-phase sequencesIndicates motor rotationChecks for open phasesFor use up to 600V2-year warranty   |
| Long Description       | 3-Phase/Motor Rotation Tester, Voltage Rating: 100 - 600 VAC (10 - 400 HZ) Nominal For Phase Presence Indication, Amperage Rating: 18 MILAMP Maximum Consumption, 3 Ph Phase, Temperature Rating: 5 - 131 DEG F Operating, -4 To 158 DEG F Storage, Display: Neon Lamps And LEDs, Dimensions: 6 IN Height X 2.8 IN Width X 1.4 IN Depth, Phase Rotary Field Direction: 1 - 600 VAC (2 - 400 HZ), Determination Of Motor Rotation: 1 - 600 VAC (2 - 400 HZ) Requires Greater Than 1/2 Turn, Over Load Protection: 550 V (Between |
| Product Type           | 3 Phase Motor Rotation Tester   |
| Special Features       | Identifies three-phase sequence; Indicates motor rotation; Checks for open phases; For use up to 600 V; Meets IEC-1010 (EN61010) safety requirements; 2-year warranty; Includes carrying case   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250615216 |
| Manufacturers Part Number | 61-521         |
| UPC                       | 783250615216   |

## Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | TEST EQUIPMENT, TESTERS AND MULTIMETERS |
| Type                 | 3-Phase/Motor Rotation Tester           |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 1.05 |

## Uses, Certifications, and Standards

|                    |   |
|--------------------|---|
| standard           | Meets IEC-1010 (EN61010) Safety Requirements, CE N12966, CAT III 600V |
| Temperature Rating | 5 - 131 DEG F Operating, -4 To 158 DEG F Storage                      |