



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **626821 Orbital Jig Saw** *Milwaukee Electric Tool*

Catalog Number	626821
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee Orbital Jig Saw 6268-21 With Led Light Provides The Ultimate Accuracy, Power, Ergonomics, and Versatility. The Saw Features An Led Light For Improved Visibility Of Sight Lines and A Precision Roller Blade Guide That Yields The Most Accurate Cuts Of Any Shape. The 6.5 Amp Motor, 1 In. Stroke With 3000 Strokes Per Minute, Tachometer Feedback, and 4 Position Orbital Cutting Action Gets The Job Done Fast Even In The Toughest Of Materials. A Cushion Grip Handle and Counter Balanced Mechanism For L
Weight per unit	9.7 (lbs/each)
Product Category	Bits, Parts, Accessories

### **Features**

blade type	Jig Saw T-Shank
Cord Length	12.66
Stroke Length	1
Voltage	120

### **Material, Color, and Finish**

Blade Material	Steel
Housing Material	Plastic

### **Dimensions and Weight**

Height	14.1
Length	9.5
Width	16



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	ORBITAL JIG SAW
extra long description	MILW 6268-21 T-shank Orbital Jig Sa
Features	Orbital Jig Saw
Long Description	The Milwaukee orbital jig saw 6268-21 with LED light provides the ultimate accuracy, power, ergonomics, and versatility. The saw features an LED light for improved visibility of sight lines and a precision roller blade guide that yields the most accurate cuts of any shape. The 6.5 amp motor, 1 in. stroke with 3000 strokes per minute, tachometer feedback, and 4 position orbital cutting action gets the job done fast even in the toughest of materials. A cushion grip handle and counter balanced mechanism for l
Product Type	T-Shank Orbital Jig Saw
Special Features	LED Light For Improved Sightline; Powerful 6.5 AMP Motor; Orbital Action With 4 Adjustment Levels And 1 IN Stroke Length For Faster Cutting; Variable Speed Trigger - 0-3,000 SPM; Variable Speed Dial For Repetitive Cuts; QUIK-LOK Blade Change System; Keyless Shoe Adjustment - 45 DEG In Both Directions; Precision Roller Blade Guide For Accurate Cuts; Counter Balanced For Reduced Vibration; Tachometer Feedback For Constant Cutting Speed; Cushion Grip For Superior Gripping And Control; Sfpm: 3000 SPM; Keyless

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242046164
Manufacturers Part Number	6268-21
UPC	045242046164

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Orbital

## Trade Size

Amperage	6.5
----------	-----

## Packaging

Carton	1
Weight Per each	9.745