SATCO NUVO

Project Name

Location Prepared By



Notes

ww1 04-14-2025 00:06:5

General		
Status	Discontinued	
Substitute	65-1210	
Fixture Type	Ceiling Wrap	
Finish	White	
Wattage	20W	
Lumen Output	1600L	
CCT (Kelvin)	3000K	_
Indoor or Outdoor Fixture	Indoor	

•	
Technology	LED
Color Temperature	Warm White
CRI	90+
Voltage	120V-277V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Non-Dimmable
Weight (lb.)	2.38
Material	Steel

Dimensions	
Height (in.)	2.63
Width (in.)	5.5
Length (in.)	24.5

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional	Information
-ce ce it di ce it di	miorimation

Warranty 5 Year Limited - Fixtures

