

Project Name

Location

Prepared By



NUVO 65-1084

4FT LED CEILING WRAP

Notes

(www) 04-14-2023 00:00:51

General

Status	Transitioning
Substitute	65-1211
Fixture Type	Ceiling Wrap
Finish	White
Wattage	40W
Lumen Output	3200L
CCT (Kelvin)	3000K
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
Color Temperature	Warm White
CRI	90+
Voltage	120V-277V
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Non-Dimmable
Weight (lb.)	4.47
Material	Steel

Dimensions

Height (in.)	2.63
Width (in.)	5.5
Length (in.)	47.5

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	No
DLC Approved	No
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
NEC Compliance	Clothes Closet Certified - Reg: 410.16 (A)(3) and 410.16 (C)(5)
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------