



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



6636GRTNK 6X6X36 Nema 3R Gutter

Unity MFG

Catalog Number	6636GRTNK
Manufacturer	Unity MFG
Description	Slip-On Cover Trough, Slip On, Gray, Low Carbon Steel, 36 In Overall Length, 6 In Overall Height, 6 In Overall Width, Powder Coated, 16 LB
Weight per unit	16.0 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

Features

Knockouts	NO
-----------	----

Dimensions and Weight

Depth	6
Length	36
Width	6

Descriptions

Description	6X6X36 NEMA 3R GUTTER
extra long description	UNT 6636GRTNK 36.00 X 6.00 X 6.00IN
Special Features	For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket

Manufacturer Information

Brand	Unity
GTIN	00761515141977
UPC	761515141977

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	GRT Gutter Slip-On Cover Wiring Trough

Packaging

Carton	1
Package	2
Weight Per each	16



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure
standard

NEMA 3R, IP32

UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant