



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 6660G 6X6X60 N1 HC Wireway W/Ko

*Unity Manufacturing*

Catalog Number	6660G
Manufacturer	Unity Manufacturing
Description	Unity 6660G Lay-In Wireway, Removable Hinged Cover Type, Length: 60 In, Width: 6 In, 6 In Height, Nema 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 16 Ga Low Carbon Steel, Gunsmoke Gray Powder Coated, Yes Knockouts, C/Us UI 50 and UI 870 - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 26 Certified, Type 1, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Termination, Ho
Weight per unit	12.5 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

### Features

Cover Type	Removable Hinged
Knockouts	Yes
Material	Low-Carbon Steel

### Material, Color, and Finish

Finish	Powder Coat
--------	-------------

### Dimensions and Weight

Height	6
Length	60
Width	6



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	Formed From Code Gauge, Low Carbon Steel
Description	6X6X60 N1 HC WIREWAY W/KO
extra long description	UNT 6660G N1 HINGED COVER WIREWAY W
Long Description	Unity 6660G Lay-In Wireway, Removable Hinged Cover Type, Length: 60 IN, Width: 6 IN, 6 IN Height, NEMA 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 16 GA Low Carbon Steel, Gunsmoke Gray Powder Coated, Yes Knockouts, C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Termination, Ho
Product Type	N1 Hinged Cover Wireway With K.O. Powder Coated
Special Features	For protecting electrical wiring where dust, dirt, oil and water are not serious problems; All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run; No pulling-through of wires or cables is required; Wireway body has mounting holes on the back; Cover is secured to the body with plated screws; Keyhole slots are furnished on the wireway cover which allow easy access to the inside without removing the screws; #10-32 x 5/16 thread forming screw; 1/2 IN, 3/4 IN

## Manufacturer Information

Brand	Unity
GTIN	00761515102909
Manufacturers Part Number	6660G
UPC	761515102909

## Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Lay-In Wireway

## Packaging

Carton	1
Package	2
Weight Per each	12.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Cable And Wire Junction, Distribution And Termination,  
Houses Runs Of Control And Power Cable

Enclosure  
standard

NEMA 1, IP30

C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use  
Primarily To Provide A Degree Of Protection Against Limited  
Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC  
60529, RoHS Compliant