



## TWO GROUNDING SINGLE-POLE COMBINATION SWITCHES, IVORY

670IG | [Pass & Seymour](#)

### FEATURES & BENEFITS

Single Pole, Double Combination Switch, 20 amp, 120/277 volt, Ivory.



- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Type: Combination, Double  
Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 0.94"  
Height (US): 3.28"  
Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 20A  
Volts: 120/277VAC  
Volts (AC): 120/277

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant





## TWO GROUNDING SINGLE-POLE COMBINATION SWITCHES, IVORY

670IG | [Pass & Seymour](#)

### FEATURES & BENEFITS

Single Pole, Double Combination Switch, 20 amp, 120/277 volt, Ivory.



- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Type: Combination, Double  
Number Of Poles: 1

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UL Listing No: 20  
UL Standard: Yes  
UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 0.94"  
Height (US): 3.28"  
Width (US): 1.32"

#### TECHNICAL INFORMATION

Amps: 20A  
Volts: 120/277VAC  
Volts (AC): 120/277

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

