



# 68547

F96T8 TL841/HO/PLUS/ALTO/TSC(PKX25)



**Application:** Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

**Base:** Recessed Double Contact (R17d)

**Coating:** Copolymer

**Color Temperature:** 4100 K

**Diameter:** 1.00 IN

**Lamp Type:** Fluorescent

**Mean Design Lumens:** 7625

**Package Weight:** 27.80 L

**Shape:** T

**Type:** Straight Linear Fluorescent Lamp

**Wattage:** 86.0 W

**Average Life Hours:** 30000

**Bulb:** T8

**Color:** TL841

**CRI:** 85

**Initial Lumens:** 8200

**Length:** 96.00 IN

**Package (LxWxH):** 96.25 IN x 6.60 IN x 6.50 IN

**Pack By:** 25

**Special Features:** Shatter-Resistant

**UPC:** 726585685479

ULEPH,ROHS,NSF Splash Zone