
68547

F96T8 TL841/HO/PLUS/ALTO/TSC(PKX25)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Average Life Hours: 30000

Base: Recessed Double Contact (R17d)

Bulb: T8

Coating: Copolymer

Color: TL841

Color Temperature: 4100K

CRI: 85

Diameter: 1.00 IN

Initial Lumens: 8200

Lamp Type: Fluorescent

Length: 96.00 IN

Mean Design Lumens: 7625

Package (LxWxH): 96.25 IN x 6.60 IN x 6.50 IN

Package Weight: 27.80 L

Pack By: 25

Shape: T

Special Features: Shatter-Resistant

Type: Straight Linear Fluorescent Lamp

UPC: 726585685479

Wattage: 86.0 W

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone