



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 690 Combo 2SWITCHES 1POLE 15A120/277V BN

*Pass & Seymour/Legrand*

Catalog Number	690
Manufacturer	Pass & Seymour/Legrand
Description	Single Pole, Double Switch, 15 Amps, 120/277 Volts, Brown.
Weight per unit	0.2110 (lbs/each)
Product Category	Combination Devices

### Features

action	(2) SP
actuator	Toggle
amperage rating	15
connection	Side wire, non-grounding
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
operating cycles	30000
Poles	1
Voltage	0.433 V
Voltage Rating	0.43321299639
Wattage	Electrical power is expressed in Amps and Volts.

### Material, Color, and Finish

Color	Brown
-------	-------

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2SWITCHES 1POLE 15A120/277V BN
extra long description	P&S 690 COMBO 2SWITCHES 1POLE 15A12
Long Description	Single Pole, Double Switch, 15 amps, 120/277 volts, Brown.
Product Type	Combo 2SWITCHES 1POLE 15A120/277V BN
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one.

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007690019
UPC	785007690019

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Non-Grounding Combination Two Single Pole Switches

### Trade Size

Amperage	15.0
----------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.211

## Uses, Certifications, and Standards

Application ..... Residential/Commercial

environmental conditions ..... Flammability: UL94 V2

Mounting ..... WALL

Operating Temperature ..... Maximum continuous +60°C, minimum -30°C

standard ..... CULUS, UL20