



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 693LA Disc Sub 693LAG, Rcd33la

*Pass & Seymour/Legrand*

Catalog Number	693LA
Manufacturer	Pass & Seymour/Legrand
Description	Double Three-Way Combination Switch, 15 Amps, 120/277 Volts, Light Almond.
Weight per unit	0.2510 (lbs/each)
Product Category	Combination Devices

### Features

action	(2) 3W
actuator	Toggle
amperage rating	15
connection	non-grounding, Side wire
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
operating cycles	30000
Poles	3-way
Voltage	0.433 V
Voltage Rating	0.43321299639
Wattage	Electrical power is expressed in Amps and Volts.

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	DISC SUB 693LAG, RCD33LA
extra long description	P&S 693LA COMBO 2SWITCHES 3WAY 15A1
Long Description	Double Three-way Combination Switch, 15 amps, 120/277 volts, Light Almond.
Product Type	Combo 2SWITCHES 3WAY 15A120/277V La
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one.

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007690194
Manufacturers Part Number	693LA
UPC	785007690194

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	COMBINATION

### Trade Size

Amperage	15.0
----------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1

Package ..... 10

Weight Per each ..... 0.251

## Uses, Certifications, and Standards

Application ..... Residential/Commercial

environmental conditions ..... Flammability: UL94 V2

Mounting ..... WALL

Operating Temperature ..... Maximum continuous +60°C, minimum -30°C

standard ..... CULUS, UL20