



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 696I Combo 2SW 1P+3W 15A 120/277V Iv

Pass & Seymour/Legrand

Catalog Number	696I
Manufacturer	Pass & Seymour/Legrand
Description	<P>Single Pole, Three-Way Combination Switch, 15 Amps, 120/277 Volts, Ivory. </P>  <P>?</P>
Weight per unit	0.2300 (lbs/each)
Product Category	Wiring Devices

### Features

action	(1) SP & (1) 3W
actuator	Toggle
amperage rating	15
connection	non-grounding, Side wire
Contact Configuration	N-O
Contact Rating	15amp, 120/277vac
operating cycles	30000
Poles	1 & 3-Way
Voltage	0.433 V
Voltage Rating	0.43321299639
Wattage	Electrical power is expressed in Amps and Volts.

### Material, Color, and Finish

Color	Ivory
-------	-------

### Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

### Descriptions

Description	COMBO 2SW 1P+3W 15A 120/277V I
extra long description	P&S 696I DISC SUB 696IG
Long Description	<p>Single Pole, Three-way Combination Switch, 15 amps, 120/277 volts, Ivory. </p>  <p>?</p>
Product Type	Disc Sub 696ig
Special Features	Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one.

### Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007696011
Manufacturers Part Number	696I
UPC	785007696011



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	COMBINATION

## Trade Size

Amperage	15.0
----------	------

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Package	10
Weight Per each	0.23

## Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20