

24V Dimmable 60W Power Supply BKT

6TD24V60BKT (Textured Black)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Ordering Information

Product ID	6TD24V60BKT
Finish	Textured Black

Specifications

Material	Metal
----------	-------

Electrical

Dimmable	Yes
Voltage	108-132V
Input Voltage	Single(120)

Qualifications

Safety Rated	Damp
Class 2	Yes
Expected Life Span	50000 Hours
Warranty	www.kichler.com/warranty

Installation

Wire Connectors	Wire Nuts
Direct Wire	Yes
Knockouts	1 in
Number of Knockouts	4

Dimensions

Height	1.25"
Length	4.50"
Width	7.25"

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

24V Dimmable 60W Power Supply BKT

6TD24V60BKT (Textured Black)

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____



Ordering Information

Product ID	6TD24V60BKT
Finish	Textured Black

Specifications

Material	Metal
----------	-------

Electrical

Dimmable	Yes
Voltage	108-132V
Input Voltage	Single(120)

Qualifications

Safety Rated	Damp
Class 2	Yes
Expected Life Span	50000 Hours
Warranty	www.kichler.com/warranty

Installation

Wire Connectors	Wire Nuts
Direct Wire	Yes
Knockouts	1 in
Number of Knockouts	4

Dimensions

Height	1.25"
Length	4.50"
Width	7.25"

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.