

# 24V Dimmable 60W Power Supply BKT

6TD24V60BKT (Textured Black)

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_



## Ordering Information

Product ID	6TD24V60BKT
Finish	Textured Black

## Specifications

Material	Metal
----------	-------

## Electrical

Dimmable	Yes
Voltage	108-132V
Input Voltage	Single(120)

## Qualifications

Safety Rated	Damp
Class 2	Yes
Expected Life Span	50000 Hours
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

## Installation

Wire Connectors	Wire Nuts
Direct Wire	Yes
Knockouts	1 in
Number of Knockouts	4

## Dimensions

Height	1.25"
Length	4.50"
Width	7.25"

### Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.

# 24V Dimmable 60W Power Supply BKT

6TD24V60BKT (Textured Black)

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Qty: \_\_\_\_\_  
Comments: \_\_\_\_\_



## Ordering Information

Product ID	6TD24V60BKT
Finish	Textured Black

## Specifications

Material	Metal
----------	-------

## Electrical

Dimmable	Yes
Voltage	108-132V
Input Voltage	Single(120)

## Qualifications

Safety Rated	Damp
Class 2	Yes
Expected Life Span	50000 Hours
Warranty	<a href="http://www.kichler.com/warranty">www.kichler.com/warranty</a>

## Installation

Wire Connectors	Wire Nuts
Direct Wire	Yes
Knockouts	1 in
Number of Knockouts	4

## Dimensions

Height	1.25"
Length	4.50"
Width	7.25"

### Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.