



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



71458802 14/2 100' UL Temp Lighttip *Southwire Company*

Catalog Number	71458802
Manufacturer	Southwire Company
Description	14/2 100'SJTW C-O-L Plas
Weight per unit	0.1300 (lbs/ft)
Product Category	Portable Cord Sets

Features

amperage rating	15
Lamp Type	A23 or larger
Number of Wires	1
Voltage Rating	125
Wattage	1875 max

Material, Color, and Finish

Color	Yellow
-------	--------

Dimensions and Weight

Size	100
------	-----

Descriptions

Description	14/2 100' UL TEMP LIGHTIP
extra long description	SWC 7145SW CORD, APPLIANCE 14/2 100
Features	Southwire™ 07145 14/2 SJTW 100-Foot Temporary Light String, 1500-Watts for Indoor/Outdoor Lighting. Cord-O-Lite 100-foot extension cord with 10 lamp holders and light sockets. Evenly spaced sockets rated for bulbs up to 150-watts each, A23 or larger. Suitable for both indoor and outdoor lighting systems, Meets OSHA, NEC Requirements, UL Listed. Temporary indoor and outdoor illumination for attics, garages, unfinished construction, and more. Lampholder spacing is 10-feet, starting 9-feet from the plug - gre
Long Description	14/2 100'SJTW C-O-L PLAS
Product Type	Cord, Appliance 14/2 100' SJTW String LT

Manufacturer Information

Brand	Cables & Cords
GTIN	00029892071455
Manufacturers Part Number	7145SW
UPC	029892071455

Taxonomies, Classifications, and Categories

Category Description	Incandescent (Except Residential)
Type	String Light



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	20
Package	100
Weight Per foot	0.13

Uses, Certifications, and Standards

Application	String Light
standard	UL Listed