



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7145SW 14/2 100' UI Temp Lightip *Southwire Company*

Catalog Number	7145SW
Manufacturer	Southwire Company
Description	Temp Lightip, Incandescent Bulb Type, 100 FT Length, Made In Usa, 1 FT Weight
Weight per unit	13.2 (lbs/ft)
Product Category	Lighting

### Features

amperage rating	15
Lamp Type	A23 or larger
Number of Wires	1
Voltage Rating	125
Wattage	1875 max

### Material, Color, and Finish

Color	Yellow
-------	--------

### Dimensions and Weight

Size	100
------	-----

### Descriptions

Description	14/2 100' UL TEMP LIGHTIP
extra long description	SWC 7145SW CORD, APPLIANCE 14/2 100
Features	Southwire™ 07145 14/2 SJTW 100-Foot Temporary Light String, 1500-Watts for Indoor/Outdoor Lighting. Cord-O-Lite 100-foot extension cord with 10 lamp holders and light sockets. Evenly spaced sockets rated for bulbs up to 150-watts each, A23 or larger. Suitable for both indoor and outdoor lighting systems, Meets OSHA, NEC Requirements, UL Listed. Temporary indoor and outdoor illumination for attics, garages, unfinished construction, and more. Lampholder spacing is 10-feet, starting 9-feet from the plug - gre

### Manufacturer Information

Brand	Cables & Cords
GTIN	00029892071455
Manufacturers Part Number	071458802
UPC	029892071455

### Taxonomies, Classifications, and Categories

Category Description	Incandescent (Except Residential)
Type	String Light



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	13.15

## Uses, Certifications, and Standards

Application	String Light
standard	UL Listed