



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7150ST 1-1/2 In Emt Comp Conn In *Appleton/Oz Gedney*

Catalog Number	7150ST
Manufacturer	Appleton/Oz Gedney
Description	Features:2IN Dia X 2 3/16IN Length, 9/16 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:1.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce
Weight per unit	0.6200 (lbs/each)
Product Category	Steel Insulated Straight Compr

### Features

connection	Male NPS Thread
Connector Type	Compression
insulation	Insulated Throat
Material	Steel

### Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

### Dimensions and Weight

Size	1.5
------	-----

### Descriptions

Description	1-1/2 IN EMT COMP CONN IN
extra long description	EGS 7150ST 1-1/2 IN EMT COMP CONN I
Long Description	Features:2IN Dia X 2 3/16IN Length, 9/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:1.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE
Product Type	1-1/2 In Emt Comp Conn Insul Steel
Special Features	2 IN Dia X 2 3/16 IN Length, 9/16 IN Thread Length, Concretetight

### Manufacturer Information

Brand	APPOZGCOMM
GTIN	00687855873449
Manufacturers Part Number	7150ST
UPC	687855873449

### Taxonomies, Classifications, and Categories

Type	EMT Conduit Straight Compression Connector
------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Trade Size ..... 1.5

## Packaging

Carton ..... 5

Package ..... 25

Weight Per each ..... 0.62

## Uses, Certifications, and Standards

Application ..... To ground and secure EMT Raceways to boxes and enclosures

nema rating ..... FB-1

standard ..... UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard:

C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507;

NEMA: FB-1

Temperature Rating ..... 90