



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7200ST 2 In Emt Comp Conn Insul Steel *Appleton/Oz Gedney*

Catalog Number	7200ST
Manufacturer	Appleton/Oz Gedney
Description	Features:2 1/4IN Dia X 2 11/16IN Length, 11/16 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:2IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated, Insulation:Insulated Throat, Temperature Rating:90ce
Weight per unit	1.0 (lbs/each)
Product Category	Steel Insulated Straight Compr

Features

connection	Male NPS Thread
Connector Type	Compression
insulation	Insulated Throat
Material	Steel

Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

Dimensions and Weight

Size	2
------	---

Descriptions

Description	2 IN EMT COMP CONN INSUL STEEL
extra long description	EGS 7200ST 2 IN EMT COMP CONN INSUL
Long Description	Features:2 1/4IN Dia X 2 11/16IN Length, 11/16 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:2IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated,Insulation:Insulated Throat, Temperature Rating:90CE
Product Type	2 In Emt Comp Conn Insul Steel
Special Features	2 1/4 IN Dia X 2 11/16 IN Length, 11/16 IN Thread Length, Concretetight

Manufacturer Information

Brand	Appleton/Oz Gedney
Manufacturers Part Number	7200ST

Taxonomies, Classifications, and Categories

Type	EMT Conduit Straight Compression Connector
------	--

Trade Size

Trade Size	2
------------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	To ground and secure EMT Raceways to boxes and enclosures
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard: C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507; NEMA: FB-1
Temperature Rating	90