



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



72C5282NP001 1-70W 120/277 MH Bal *Advance By Signify*

Catalog Number	72C5282NP001
Manufacturer	Advance By Signify
Description	Versatility In Commercial Applications Low Noise For Indoor Use;Two Dual Voltage Configurations Available: 120V/277V For The U.S Market and 120V/347V For The Canadian Market The Philips Advance Line Of F-Can Hid Ballasts Comes In Two Dual-Voltage Configurations For The Us and Canadian Market. Ballasts For These Luminaires Are Most Often Encased and Potted In Fluorescent Ballast Type Cans. Utilizes UI Class A (90°C) Insulation;Has Built-In, Automatically Resetting, Thermal Protector Which Disconnects The Ba
Weight per unit	8.9 (lbs/each)
Product Category	Pulse Start Hid Ballasts

Features

amperage rating	1.25/0.55
ANSI Code	M98/143
Ballast Factor	1
Circuit Type	HX-HPF
Lamp Type	METAL HALIDE
Number of Lamps	1
Power Factor	0.90
Power Rating	70
start type	Pulse
Voltage Rating	120/277
Wattage	70
Wire Length	12
Wire Type	STRANDED

Material, Color, and Finish

Housing Material	Metal
------------------	-------

Dimensions and Weight

Height	1.02
Length	0.47
Width	1.54



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	1-70W 120/277 MH BAL
extra long description	ADV 494112 MH BAL 70W M98/143 120/2
Long Description	Versatility in commercial applications Low noise for indoor use;Two dual voltage configurations available: 120V/277V for the U.S market and 120V/347V for the Canadian market The Philips Advance line of F-can HID ballasts comes in two dual-voltage configurations for the US and Canadian market. Ballasts for these luminaires are most often encased and potted in fluorescent ballast type cans. Utilizes UL Class A (90°C) insulation;Has built-in, automatically resetting, thermal protector which disconnects the ba
Product Type	MH Bal 70W M98/143 120/277V Fcan
Special Features	Suitable for Outdoor; UL, CSA, RoHS

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087025253
Manufacturers Part Number	494112
UPC	781087025253

Taxonomies, Classifications, and Categories

Category Description	HID BALLASTS
Type	Magnetic HID

Packaging

Carton	1
Weight Per each	8.86

Uses, Certifications, and Standards

Frequency Rating	60
standard	CSA certificate;UL certificate;RoHS Compliant