

# Stinger® LED Rechargeable Flashlight

Case Material: 6000 series machined aircraft aluminum with non-slip rubberized comfort grip and anti-roll rubber ring.

Dimensions: Length: 8.41 in. (21.36 cm) Diameter: Major Diameter: 1.62 in. (4.11 cm)  
Body Diameter: 1.17 in. (2.97 cm)

Weight: 12.4 oz (352 grams)\*

Lens: Unbreakable polycarbonate lens with scratch-resistant coating

Light Source: C4 LED technology, shock-proof with a 50,000 hour lifetime.

Light Output: Up to 18,000 candela (peak beam intensity); up to 160 lumens measured system output. Deep-dish parabolic reflector produces a long range targeting beam with optimum peripheral illumination to aid in navigation. Optimized electronics provides regulated intensity.

On/Off: Multi-function, easy access push-button switch designed for extremely long life; tested at 1 million actuations

Run Time: High brightness: 1.75 continuous hours  
Medium brightness: 3.5 continuous hours  
Low brightness: 6.75 continuous hours

Battery: 3-Cell, 3.6-Volt Nickel-cadmium sub-C battery is rechargeable up to 1000 times

Charging: Ten hours to fully recharge on 100V, 120V, 230V or 240V AC, or 12V DC, 2.5-hour fast charger or PiggyBack® charger model available

Features: • Anti-roll ring included • LED charge-continuity indicator, compact  
• Snap-in charger holder that mounts in any position • Serialized for positive identification

Approvals\*\*: Most models meet applicable European Community Directives.

Warranty: Limited lifetime warranty

\*With battery (included in purchase).

\*\*See product for specific ratings.



Item	UPC	Part #
Steady Charge AC/DC - 2 Holders		
Stinger LED with 230V	080926-75725-7	75725
Stinger LED with 240V	080926-75729-5	75729
Stinger LED with 120V	080926-75713-4	75713
Stinger LED with 100V	080926-75718-9	75718
AC Only		
Stinger LED with 230V	080926-75724-0	75724
Stinger LED with 240V	080926-75728-8	75728
Stinger LED with 120V	080926-75711-0	75711
Stinger LED with 100V	080926-75717-2	75717
DC Only		
Stinger LED with DC	080926-75712-7	75712
Stinger LED with DC PiggyBack	080926-75734-9	75734
Stinger LED with DC Fast Charger	080926-75715-8	75715
Stinger LED with DC - FC PiggyBack	080926-75737-0	75737
Steady Charge AC/DC PiggyBack		
Stinger LED with 230V	080926-75739-4	75739
Stinger LED with 240V	080926-75743-1	75743
Stinger LED with 120V	080926-75732-5	75732
Stinger LED with 100V	080926-75732-5	75746
AC - PiggyBack Holder		
Stinger LED with 230V	080926-75738-7	75738
Stinger LED with 240V	080926-75742-2	75742
Stinger LED with 120V	080926-75733-2	75733
Stinger LED with 100V	080926-75721-9	75721
See reverse for additional part numbers		

Item	UPC	Part #
AC/DC Fast Charger - 2 Holders		
Stinger LED with 230V	080926-75727-1	75727
Stinger LED with 240V	080926-75731-8	75731
Stinger LED with 120V	080926-75735-6	75735
Stinger LED with 100V	080926-75720-2	75720
AC Fast Charger		
Stinger LED with 230V	080926-75726-4	75726
Stinger LED with 240V	080926-75730-1	75730
Stinger LED with 120V	080926-75714-1	75714
Stinger LED with 100V	080926-75719-6	75719
AC/DC - Fast Charger PiggyBack Holder		
Stinger LED with 230V	080926-75741-7	75741
Stinger LED with 240V	080926-75716-5	75745
Stinger LED with 120V	080926-75716-5	75716
Stinger LED with 100V	080926-75747-9	75747
AC - Fast Charger PiggyBack Holder		
Stinger LED with 230V	080926-75740-0	75740
Stinger LED with 240V	080926-75744-8	75744
Stinger LED with 120V	080926-75736-3	75736
Stinger LED with 100V	080926-75722-6	75722
(WITHOUT CHARGER)		
Stinger LED	080926-75710-3	75710
See reverse for additional part numbers		