



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



7580 R Duplex 15A 125V 10A 250V T/L

Pass & Seymour/Legrand

Catalog Number	7580
Manufacturer	Pass & Seymour/Legrand
Description	Receptacle Duplex 15A 125V 10A 250V Turnlok Registered
Weight per unit	0.3040 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15/10
Material	Nylon
Number of Wires	3
Poles	Consult the Factory
Voltage	125.0 V
Voltage Rating	125/250
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	Consult the Factory

Dimensions and Weight

Height	4.031
Width	1.199

Descriptions

Description	R DUPLEX 15A 125V 10A 250V T/L
extra long description	P&S 7580 R DUP 15A 125V 10A 250V T/
Long Description	Receptacle Duplex 15A 125V 10A 250V Turnlok Registered
Product Type	R Dup 15A 125V 10A 250V T/L
Special Features	Impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength. One piece, high-grade contacts offer excellent conductivity and heat-rise resistance. Clearly marked rating on each unit's face. Single-piece mounting strap is free of easily loosened rivets found on other brands.

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007758009
Manufacturers Part Number	7580
UPC	785007758009

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Turnlok® Receptacle, Non-NEMA

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	50
Weight Per each	0.304

Uses, Certifications, and Standards

Application	Industrial
environmental conditions	Consult the Factory
Mounting	WALL
nema rating	Non-NEMA
standard	Non-NEMA