



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



75ARS130PK6 *Delisted* 75W 130V Rough Service Proline Incan

Ge By Current Lamps

Catalog Number	75ARS130PK6
Manufacturer	Ge By Current Lamps
Description	A-Line Incandescent Lamp, 740 LM Brightness (Lumens), 75 W, 130 V, Inside Frost, C-7A Filament, 2000 H Average Life, E26 Medium Screw Base, Non Dimmable, 1.25 In Diameter, 4.43 In Length, 0.11 LB
Weight per unit	0.1100 (lbs/each)
Product Category	Line A, P, PS Shape Lamps

Features

Base	Medium Screw (E26)
lumens	740
Voltage Rating	130
Wattage	75

Material, Color, and Finish

Color	INSIDE FROST
-------	--------------

Dimensions and Weight

Diameter	1.25
----------	------

Descriptions

Description	*DELISTED* 75W 130V ROUGH SERVICE PROLINE INCAN
-------------	---

Manufacturer Information

Brand	GE Current
GTIN	00043168725309
Manufacturers Part Number	75A/RS/130-PK6
UPC	043168725309

Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
----------------------	--------------

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Package	6
Weight Per each	0.11