



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7731WBOX SW Deco Comb 3WAY/3WAY 15A 120/277V WH

*Eaton Wiring Devices*

Catalog Number	7731WBOX
Manufacturer	Eaton Wiring Devices
Description	Eaton Commercial Grade Combination Switch, Auto-GRND, Decorator, #14 - #12 Awg, 15A, Resi, Comm, 120/277V, BK and SD Wiring, Rocker, Maint Closure, Screw, Brass, WHT, -20-60°C, (2) 3-Way, DPLX, Thermoplas, Polycrb, PVC
Weight per unit	0.2450 (lbs/each)
Product Category	Gen Purpose Switches

### Features

dimensions	1.8850 IN X 1.8050 IN X 4.3140 IN
------------	-----------------------------------

### Descriptions

Description	SW DECO COMB 3WAY/3WAY 15A 120/277V WH
extra long description	EWD 7731W-BOX SW Deco Comb 3Way/3Wa
Features	Eaton's Arrow Hart commercial specification grade switches are designed to provide superior quality, reliability and performance in a variety of commercial environments.
Long Description	Eaton commercial grade combination switch, auto-grnd, Decorator, #14 - #12 AWG, 15A, resi, comm, 120/277V, bk and sd wiring, Rocker, Maint closure, Screw, Brass, wht, -20-60°C, (2) 3-way, dplx, thermoplas, polycrb, PVC
Product Type	SW Deco Comb 3WAY/3WAY 15A 120/277V WH
Special Features	Combination devices deco

### Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664664908
Manufacturers Part Number	7731W-BOX
UPC	032664664908

### Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Commercial grade combination switch

### Packaging

Carton	10
Package	80
Weight Per each	0.245



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

standard

NOM,cULus Listed