



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 774005 Toggle Switch, DPST, On-Off, Spade

*Ideal*

Catalog Number	774005
Manufacturer	Ideal
Description	Ideal, Toggle Switch, Heavy-Duty, On-Off, Voltage Rating: 125, 227 Vac, Number Of Poles: 2, Amperage Rating: 20, 10 Amp, Action: DPST, Connection: Spade, 4 Terminals, Actuator: Toggle, Contact Rating: Factory Tested 100000 Cycles to 21 Amp 14.8 VDC DC Rating, Size: 1.300 In Length X 0.760 In Width X 0.800 In Height, Mounting: 1/2 In Hole Diameter, Operating Cycles: 100000 Cycles Mechanical Life, Operating Temperature: 32 to 185 Deg F, Dielectric Strength: 1500 V, Finish: Solid Brass/Nickel-Plated Bushings,
Weight per unit	N/A
Product Category	Gen Purpose Switches

### Features

action	DPST
amperage rating	20,10
connection	Spade, 4 Terminals
Contact Rating	Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating
operating cycles	100000
Poles	2
Switch Type	Toggle
Voltage Rating	125, 227

### Dimensions and Weight

Height	0.800
Width	0.760



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	TOGGLE SWITCH, DPST, ON-OFF, SPADE
extra long description	IDEAL 774005 SWITCH,TGL,DPST,O-F,SP
Features	Great for power tool and motor control switch applicationsRugged long-wearing solid brass/nickel-plated bushings1/2 in. diameter mounting holeDielectric Strength: 1500VMechanical Life: 100,000 cyclesOperating Temperature: 32°F to 185°F (0°C to 85°C)DC?Rating: Factory tested 100,000 cycles to 21 Amp 14.8 VDC
Long Description	IDEAL, Toggle Switch, Heavy-Duty, On-OFF, Voltage Rating: 125, 227 VAC, Number Of Poles: 2, Amperage Rating: 20, 10 AMP, Action: DPST, Connection: Spade, 4 Terminals, Actuator: Toggle, Contact Rating: Factory Tested 100000 Cycles To 21 AMP 14.8 VDC DC Rating, Size: 1.300 IN Length X 0.760 IN Width X 0.800 IN Height, Mounting: 1/2 IN Hole Diameter, Operating Cycles: 100000 Cycles Mechanical Life, Operating Temperature: 32 To 185 DEG F, Dielectric Strength: 1500 V, Finish: Solid Brass/Nickel-Plated Bushings,
Product Type	Switch, TGL, DPST, O-F, SPD
Special Features	1/2 IN Diameter Mounting Hole;Bulk Packaging Of 100 Available Upon Request;DC Rating: Factory Tested 100000 Cycles To 21 AMP 14.8 VDC;Dielectric Strength: 1500 V;Features: Great For Power Tool And Motor Control Switch Applications;Finish: Solid Brass/Nickel-Plated Bushings;Hp Rating: 1-1/2 HP At 125 To 250 VAC;Mechanical Life: 100000 Cycles;Operating Temperature: 32 DEG F To 185 DEG F (0 DEG C To 85 DEG C);Rugged Long-Wearing Solid Brass/Nickel-Plated Bushings

## Manufacturer Information

Brand	Ideal
Manufacturers Part Number	774005

## Taxonomies, Classifications, and Categories

Category Description	TOGGLE SWITCHES
Type	Heavy-Duty, On-OFF

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	0



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	For Power Tool And Motor Control Switch Applications .....
Mounting .....	1/2 IN Hole Diameter .....
standard .....	CSA, RU Listed, RoHS .....